


Insert label - US-EMT (23X109) - 0803858

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, insert label, for marking Siemens S-7-1500 controllers, card, white, unmarked, can be marked with: THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 23 x 109 mm



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 055626 172927 |
| GTIN | 4055626172927 |
| Weight per Piece (excluding packing) | 5.990 g |
| Custom tariff number | 39204910 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|--------|
| Length (b) | 109 mm |
| Width (a) | 23 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

General

| | |
|-------------------------------------|--------------------------------|
| Color | white |
| Components | free from silicone and halogen |
| Material | Polyester |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 4 |
| Number of individual labels per row | 4 |
| Marking mounting type | snapped into marker carrier |

Insert label - US-EMT (23X109) - 0803858

Technical data

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 5.0 | 27149100 |
| eCl@ss 5.1 | 27149100 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149129 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

Accessories

Accessories

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards