

PROCAP5



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems
→ Terminal Block Markers

General Information

Extended Product Type:	PROCAP5
Product ID:	1SNK900609R0000
EAN:	3472599097414
Catalog Description:	PROCAP5 Protecting cap for SAT5 labels
Long Description:	- Easily protect your Self Adhesive sTrip SAT, - Quickly put it on the terminal blocks: PROCAP delivered in strip of 10 parts

Ordering

Color:	Transparent
---------------	-------------

Minimum Order Quantity:	20 piece
--------------------------------	----------

Customs Tariff Number:	39269097
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNK160013D0201
---	-----------------

Instructions and Manuals:	1SNK160027C0205
----------------------------------	-----------------

Dimensions

Product Net Width:	5.2 mm
---------------------------	--------

Product Net Height:	12 mm
----------------------------	-------

Product Net Length:	2.4 mm
----------------------------	--------

Product Net Depth / Length:	2.4 mm
------------------------------------	--------

Product Net Weight:	0.7 g
----------------------------	-------

Technical

Spacing:	5.2 mm
-----------------	--------

Function:	Protecting cap
------------------	----------------

Pollution Degree:	3
--------------------------	---

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

Insulation Material:	Polycarbonate
-----------------------------	---------------

Suitable For:	C2.5-ZDP CDK2.5 CDK4 CDS4 CDS4-R1 ES-TC PG5 S-17
----------------------	---

SAI
TC5
ZDK2.5-22
ZDS4-22
ZK10
ZK10-PE
ZK16
ZK16-PE
ZK2.5
ZK2.5-3P
ZK2.5-4P
ZK2.5-D1
ZK2.5-D1-PE
ZK2.5-D2
ZK2.5-D2-PE
ZK2.5-D-CH
ZK2.5-PE
ZK2.5-PE-3P
ZK2.5-PE-4P
ZK2.5-S
ZK2.5-SF
ZK2.5-SF-R
ZK2.5-SP
ZK2.5-S-R1
ZK4
ZK4-3P
ZK4-4P
ZK4-PE
ZK4-PE-3P
ZK4-PE-4P
ZK6
ZK6-3P
ZK6-PE
ZK6-PE-3P
ZS4
ZS4-D1
ZS4-D2
ZS4-D2-S
ZS4-D2-S-T
ZS4-D-CH
ZS4-PE
ZS4-S
ZS4-SP
ZS4-SP-T2
ZS4-S-T
ZS4-T3
ZS4-T3-R1

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225156C1000
Environmental Information:	1SND220061E1000
Instructions and Manuals:	1SNK160027C0205
RoHS Information:	1SND230504F0204

Classifications

Object Classification Code:	X
E-nummer:	2967973
ETIM 4:	EC000761 - Labelling for terminal block
ETIM 5:	EC000761 - Labelling for terminal block
ETIM 6:	EC000761 - Labelling for terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	158 mm
Package Level 1 Depth / Length:	243 mm
Package Level 1 Gross Weight:	0.014 kg
Package Level 1 EAN:	3472599097414
Package Level 2 Units:	10000 piece
Package Level 3 Units:	320000 piece
Product Packing Type:	Bag

