CyberPower

CSHT808TC HOME THEATER SURGE PROTECTOR

Powerful surge protection for your home theater equipment

The CyberPower Home Theater Series CSHT808TC Surge Protector is ideal for home entertainment and home office protection. With 2850 joules, it offers premium protection for HDTVs, cable/satellite receivers, personal computers, cable modems, phones, printers, stereos, and CD/DVD players.

The CSHT808TC features 8 surge-protected outlets, including 4 widely-spaced outlets to accommodate larger plugs and an 8-foot cord. The EMI/RFI filters block unwanted line noise for better picture • 8 Surge Protected Outlets and sound quality. MOV technology diverts any surges/spikes through the ground circuit to safeguard connected electronics and the surge suppressor. Data line inputs provide protection for networking and telecommunication devices.

A Limited Lifetime Warranty and \$300,000 Connected Equipment Guarantee ensures this surge protector has passed our highest quality standards in design, assembly, material or workmanship.

TYPICAL APPLICATIONS

- HDTVs
- Desktop Computers
- Personal Electronics
- Cable/Satellite Receivers

FEATURES

- 2850 Joules of Surge Protection
- RJ11 Ports for DSL / Phone / Fax Protection
- Coax (RG6) Ports for Cable / Satellite Protection

Cyber Power

- 15A Circuit Breaker
- 8 ft. Cord with Low Profile Right Angle Plug
- EMI/RFI Noise Filters
- Outlet Dust Covers
- Lifetime Warranty

SPECIFICATIONS

INPUT	
Voltage	125 V
Switch	Non-Lighted On/Off - Reset
Plug Type	NEMA 5-15P
Plug Style	Low Profile Right Angle - 45° Offset
Circuit Breaker	15A
Cord Length	8 ft
OUTPUT	
Outlet Type	NEMA 5-15R
Outlets - Total	8 (4 standard, 4 wide-spaced)
SURGE PROTECTION & FILTERING	
Surge Suppression	2,850 joules
Maximum Surge Current	135,000 amps
Maximum Surge Current (H-N)	75,000 amps

Maximum Surge Current (H-G/N-G)	30,000 amps	
Clamping Voltage (L-N, L-G, N-G)	400V	
Response Time	<1 nanosecond	
EMI/RFI Filtration	150 kHz - 100 MHz	
Attenuation	Up to 43dB	
Communication Protection	RJ11 1-In / 2-Out; Coax RG6 1 Pair	
CERTIFICATIONS		
Safety	UL1363 / 1449 3rd Edition, cUL	
Environmental	RoHS Compliant	
WARRANTY		
Product Warranty	Limited Lifetime	
Connected Equipment Guarantee	Lifetime	
CEG Amount	\$300,000	

©2019 Cyber Power Systems (USA), Inc. CyberPower is a registered trademark and brand of Cyber Power Systems (USA), Inc. All rights reserved. All other trademarks are the property of their respective owners. CyberPower reserves the right to change, without notice, marketing programs, product offerings and specifications. www.cyberpowersystems.com