

Housing screw connection - SACC-FP-F-M8/M10 SMD - 1412504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




M8 female connector, front mounting SMD with M10 screw fastening

Your advantages

- ✓ Reduced mounting costs thanks to two-piece device connector
- ✓ Easy device integration, thanks to mechanical port screw connections with threaded fastening
- ✓ Efficient PCB assembly: two-piece connectors for SMT soldering

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 989077
GTIN	4046356989077
Weight per Piece (excluding packing)	4.160 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (without mechanical actuation)
Degree of protection	IP67 (correctly plugged in and locked)

General

Note	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Standards/regulations	M8 connector In line with

Housing screw connection - SACC-FP-F-M8/M10 SMD - 1412504

Technical data

General

Mounting type	Front mounting M10 x 0.75
---------------	---------------------------

Material

Material, knurls	Nickel-plated brass
Material	Brass, nickel-plated
Sealing material	FKM (O-ring on housing)
	FKM (O-ring (pin connector pattern))

Cable

Standards/specifications	M8 connector In line with
--------------------------	---------------------------

Standards and Regulations


Standard designation	M8 connector
----------------------	--------------

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Housing screw connection - SACC-FP-F-M8/M10 SMD - 1412504

Classifications

eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

ETIM

ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

UNSPSC

UNSPSC 13.2	39121421
-------------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	--	---------

Accessories

Accessories

Panel mounting base

Housing screw connection - SACC-FP-F-M8/M10 SMD - 1412504

Accessories

Nut - SACC-M10-NUT - 1412508



M10 flat nut

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>