

PRODUCT-DETAILS

E3N3200PR121/P-LSI In=3200A3pFHR

E3N 3200 PR121/P-LSI In=3200A 3p F HR



General Information

Extended Product Type	E3N3200PR121/P-LSI In=3200A3pFHR
Product ID	1SDA056145R1
EAN	8015644574857
Catalog Description	E3N 3200 PR121/P-LSI In=3200A 3p F HR
Long Description	SACE EMAX CIRCUIT-BREAKER E3N 3200A THRE-POLE FIXED WITH TERMINALS REAR HORIZONTAL OVERCURRENT RELEASE PR121/P-LSI R3200 FITTED WITH: 4 AUXILIARY CONTACT AND C.BREAKER IN POSITION OPEN-CLOSED

Ordering

EAN	8015644574857
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	404 mm
Product Net Height	418 mm
Product Net Depth / Length	302 mm
Product Net Weight	60 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	515 mm
Package Level 1 Height	600 mm
Package Level 1 Depth / Length	615 mm
Package Level 1 Gross Weight	72 kg
Package Level 1 EAN	8015644574857

Additional Information

Current Type	AC
Electrical Durability	Ue = < 440 V 6000 cycle Ue = 500 ... 690 V 5000 cycle 20 cycles per hour
Mechanical Durability	20000 cycle 60 cycles per hour
Number of Poles	3
Power Loss	330 W
Product Main Type	SACE Emax
Product Name	Air Circuit Breaker
Product Type	Air Circuit Breaker
Rated Current (I _n)	3200 A
Rated Voltage (U _r)	690 V
Rated Impulse Withstand Voltage (U _{imp})	12 kV
Rated Insulation Voltage (U _i)	1000 V
Rated Operational Current (I _e)	3200 A
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity (I _{cs})	(220 V AC) 65 kA (230 V AC) 65 kA (380 V AC) 65 kA (400 V AC) 65 kA (415 V AC) 65 kA (440 V AC) 65 kA (500 V AC) 65 kA (660 V AC) 65 kA (690 V AC) 65 kA
Rated Short-time Withstand Current (I _{cw})	for 1 s 65 kA for 3 s 65 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu})	(220 V AC) 65 kA (230 V AC) 65 kA (380 V AC) 65 kA (400 V AC) 65 kA (415 V AC) 65 kA (440 V AC) 65 kA (500 V AC) 65 kA (660 V AC) 65 kA (690 V AC) 65 kA
Rated Uninterrupted Current (I _u)	3200 A
Release Type	EL
Standards	IEC
Sub-type	E3
Terminal Connection Type	Fixed Circuit-Breakers Rear flat Horizontal
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC200006D0209
Declaration of Conformity - CE	1SDL000165R0015
Environmental Information	1SDL000145R0
Instructions and Manuals	1SDH000460R0002

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Air Circuit Breakers → Emax

