


Plastic cable markers - KMK 2-1000 - 0815004

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable binders, cable diameter: \geq 6 mm, lettering field size: 29 x 8 mm



Key Commercial Data

Packing unit	1000 pc
Minimum order quantity	1000 pc
GTIN	 4 046356 014212
GTIN	4046356014212
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	29 mm
Width (a)	8 mm
Height (c)	8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Type	Mounting set
Components	free from silicone and halogen
Material	Polyethylene
Marking mounting type	Assembly with cable binders

Plastic cable markers - KMK 2-1000 - 0815004

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Cable tie

Cable tie - WT-HF 2,5X98 - 3240732



Cable binders for quick and secure bundling, standard version

Plastic cable markers - KMK 2-1000 - 0815004

Accessories

Cable tie - WT-HF 2,6X160 - 3240736



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,6X200 - 3240740



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X140 - 3240744



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X200 - 3240748



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X200 BK - 3240749



Cable binders for quick and secure bundling, standard version

Plastic cable markers - KMK 2-1000 - 0815004

Accessories

Cable tie - WT-HF 3,6X290 - 3240752



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,5X98 BK - 3240733



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,6X160 BK - 3240737



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,6X200 BK - 3240741



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X140 BK - 3240745



Cable binders for quick and secure bundling, standard version

Plastic cable markers - KMK 2-1000 - 0815004

Accessories

Cable tie - WT-HF 3,6X200 BK - 3240749



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X290 BK - 3240753



Cable binders for quick and secure bundling, standard version

Conductor marking

Insert label - EMT (29X8)R - 0817277



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm, Number of individual labels: 5400

Device marking

Snap-in markers - US-EMP (29X8) - 0829436



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 29 x 8 mm, Number of individual labels: 48

Labeled conductor marker

Insert label - EMT (29X8)R CUS - 0824383



Insert label, can be ordered: by line, white, labeled according to customer specifications, mounting type: insert, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm

Labeled terminal marker

Plastic cable markers - KMK 2-1000 - 0815004

Accessories

Insert strip - ESL 29X8 CUS - 0824401



Insert strip, can be ordered: Sheet, white, labeled according to customer specifications, mounting type: insert, lettering field size: 29 x 8 mm

Terminal marking

Insert strip - ESL 29X8 - 0808257



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, perforated, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 174