

PRODUCT-DETAILS

RB121G-24VDC

RB121G-24VDC Interface relay R600 1c/o,A1-A2=24VDC,5-250VAC/10mA-6A



General Information

| | |
|-----------------------|---|
| Extended Product Type | RB121G-24VDC |
| Product ID | 1SNA645072R0000 |
| EAN | 4013614508141 |
| Catalog Description | RB121G-24VDC Interface relay R600 1c/o,A1-A2=24VDC,5-250VAC/10mA-6A |
| Long Description | Screw relay RB121G-24VDC: 24VDC Rated control supply voltage/ 1 SPDT gold plated output contact rated 5-250VAC, 10mA up to 6A with integrated LED |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 10 piece |
| Customs Tariff Number | 85364900 |

Popular Downloads

| | |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SVC117001D0200 |
| Instructions and Manuals | 1SVC645000M9000 |

Dimensions

| | |
|--------------------|---------|
| Product Net Width | 6 mm |
| Product Net Height | 67.5 mm |

| | |
|----------------------------|---------|
| Product Net Depth / Length | 70 mm |
| Product Net Weight | 0.02 kg |

Technical

| | |
|--|----------------------------|
| Function | Boxed interface relay R600 |
| Sub-Function | Relay with built in LED |
| Output | 1 c/o (SPDT) contact |
| Output Signal | 5 ... 250VAC / 10mA ... 6A |
| Rated Control Supply Voltage (U _s) | 24 V DC |
| Terminal Type | Screw Terminals |

Environmental

| | |
|-------------|-----------------------------------|
| RoHS Status | Following EU Directive 2011/65/EU |
|-------------|-----------------------------------|

Certificates and Declarations (Document Number)

| | |
|--------------------------------|--------------------------|
| CB Certificate | CB_DK-53188-UL |
| CCC Certificate | CCC_2017010303941444 |
| CSA Certificate | CSA_254821 |
| cUR Certificate | cUR_E352056 |
| Declaration of Conformity - CE | 1SVD982016-0001 |
| EAC Certificate | EAC_RU_C-FR.ME77.B.01634 |
| Instructions and Manuals | 1SVC645000M9000 |
| LR Certificate | LR_16_20068 |
| RoHS Information | 1SVD982016-0001 |
| UR Certificate | UR_E352056 |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 10 piece |
| Package Level 1 Width | 73 mm |
| Package Level 1 Height | 71 mm |
| Package Level 1 Depth / Length | 80 mm |
| Package Level 1 Gross Weight | 0.23 kg |
| Package Level 1 EAN | 3472596450724 |

Classifications

| | |
|----------------------------|----------------------------|
| Object Classification Code | K |
| ETIM 4 | EC001437 - Switching relay |
| ETIM 5 | EC001437 - Switching relay |
| ETIM 6 | EC001437 - Switching relay |
| ETIM 7 | EC001437 - Switching relay |
| eClass | 7.0 27371601 |

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

