

RoHS  
Compliant



## Specifications:

Application : Electronics and Solderless Wrap Connections  
 Multi construction : Single Solid Core

### Construction

Conductor : Silver Plated Solid Copper  
 Jacket : ETFE  
 Nom.Thickness : 0.15mm  
 Jacket Colour : White, Black, Red, Green, Yellow, Blue, Brown, Orange, Grey and Purple  
 Packaging : 50m/Reel

### Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)

24AWG	87.9
26AWG	140
28AWG	223
30AWG	354

Rated Temperature : -65°C to +160°C  
 Rated Voltage : 300V  
 Insulation DC Resistance at 20°C (MΩ × kM) : >500

Part Number	PP000671	PP000672	PP000673	PP000674	PP000675	PP000676	PP000677	PP000708	PP000709	PP000710
AWG	24									
Conductor	0.51mm									
Jacket (mm)	0.81 ±0.05									

Part Number	PP000681	PP000682	PP000683	PP000684	PP000685	PP000686	PP000687	PP000678	PP000679	PP000680
AWG	26									
Conductor	0.404mm									
Jacket (mm)	0.7 ±0.05									

# ETFE High-Temperature Wire



<b>Part Number</b>	PP000691	PP000692	PP000693	PP000694	PP000695	PP000696	PP000697	PP000688	PP000689	PP000690
<b>AWG</b>	28									
<b>Conductor</b>	0.32mm									
<b>Jacket (mm)</b>	0.62 ±0.05									

<b>Part Number</b>	PP000701	PP000702	PP000703	PP000704	PP000705	PP000706	PP000707	PP000698	PP000699	PP000700
<b>AWG</b>	30									
<b>Conductor</b>	0.254mm									
<b>Jacket (mm)</b>	0.55 ±0.03									

## Part Number Table

Description	Part Number
Wire, 50m, 24AWG, SPC, Green, 0.81mm	PP000671
Wire, 50m, 26AWG, SPC, Green, 0.7mm	PP000681
Wire, 50m, 28AWG, SPC, Green, 0.62mm	PP000691
Wire, 50m, 30AWG, SPC, Green, 0.55mm	PP000701
Wire, 50m, 24AWG, SPC, Yellow, 0.81mm	PP000672
Wire, 50m, 26AWG, SPC, Yellow, 0.7mm	PP000682
Wire, 50m, 28AWG, SPC, Yellow, 0.62mm	PP000692
Wire, 50m, 30AWG, SPC, Yellow, 0.55mm	PP000702
Wire, 50m, 24AWG, SPC, Blue, 0.81mm	PP000673
Wire, 50m, 26AWG, SPC, Blue, 0.7mm	PP000683
Wire, 50m, 28AWG, SPC, Blue, 0.62mm	PP000693
Wire, 50m, 30AWG, SPC, Blue, 0.55mm	PP000703
Wire, 50m, 24AWG, SPC, Brown, 0.81mm	PP000674
Wire, 50m, 26AWG, SPC, Brown, 0.7mm	PP000684
Wire, 50m, 28AWG, SPC, Brown, 0.62mm	PP000694
Wire, 50m, 30AWG, SPC, Brown, 0.55mm	PP000704
Wire, 50m, 24AWG, SPC, Orange, 0.81mm	PP000675
Wire, 50m, 26AWG, SPC, Orange, 0.7mm	PP000685
Wire, 50m, 28AWG, SPC, Orange, 0.62mm	PP000695
Wire, 50m, 30AWG, SPC, Orange, 0.55mm	PP000705

Description	Part Number
Wire, 50m, 24AWG, SPC, Grey, 0.81mm	PP000676
Wire, 50m, 26AWG, SPC, Grey, 0.7mm	PP000686
Wire, 50m, 28AWG, SPC, Grey, 0.62mm	PP000696
Wire, 50m, 30AWG, SPC, Grey, 0.55mm	PP000706
Wire, 50m, 24AWG, SPC, Violet, 0.81mm	PP000677
Wire, 50m, 26AWG, SPC, Violet, 0.7mm	PP000687
Wire, 50m, 28AWG, SPC, Violet, 0.62mm	PP000697
Wire, 50m, 30AWG, SPC, Violet, 0.55mm	PP000707
Wire, 50m, 26AWG, SPC, White, 0.7mm	PP000678
Wire, 50m, 28AWG, SPC, White, 0.62mm	PP000688
Wire, 50m, 30AWG, SPC, White, 0.55mm	PP000698
Wire, 50m, 24AWG, SPC, White, 0.81mm	PP000708
Wire, 50m, 26AWG, SPC, Black, 0.7mm	PP000679
Wire, 50m, 28AWG, SPC, Black, 0.62mm	PP000689
Wire, 50m, 30AWG, SPC, Black, 0.55mm	PP000699
Wire, 50m, 24AWG, SPC, Black, 0.81mm	PP000709
Wire, 50m, 26AWG, SPC, Red, 0.7mm	PP000680
Wire, 50m, 28AWG, SPC, Red, 0.62mm	PP000690
Wire, 50m, 30AWG, SPC, Red, 0.55mm	PP000700
Wire, 50m, 24AWG, SPC, Red, 0.81mm	PP000710

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

