

## Adapter insert - SF-UBH - 1212590

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Universal bit holder, E6.3-1/4" drive, with automatic locking, one-hand operation, magnetic, suitable for bits according to DIN 3126 C6.3 and E6.3

### Your advantages

- ✔ Tools for SF-ASD 21 cordless screwdriver in various versions

### Key Commercial Data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 1 pc   |
| GTIN                                 | <br>4 046356 590259 |
| GTIN                                 | 4046356590259  |
| Weight per Piece (excluding packing) | 34.000 g   |
| Custom tariff number                 | 84661038   |
| Country of origin                    | Czech Republic   |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 50 mm |
|------------|-------|

#### General

|          |                    |
|----------|--------------------|
| Color    | silver             |
| Type     | Hexagonal          |
| Material | alloyed tool steel |

#### Environmental Product Compliance

|                           |   |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 21044290 |
| eCl@ss 4.0    | 21040400 |
| eCl@ss 4.1    | 21040400 |

# Adapter insert - SF-UBH - 1212590

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.0 | 21040400 |
| eCl@ss 5.1 | 21040400 |
| eCl@ss 6.0 | 21049200 |
| eCl@ss 7.0 | 21044290 |
| eCl@ss 8.0 | 21049290 |
| eCl@ss 9.0 | 21044290 |

### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC002118 |
| ETIM 5.0 | EC002118 |
| ETIM 6.0 | EC002118 |
| ETIM 7.0 | EC002118 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 27111701 |
| UNSPSC 7.0901 | 27111701 |
| UNSPSC 11     | 27111701 |
| UNSPSC 12.01  | 27111701 |
| UNSPSC 13.2   | 27112832 |
| UNSPSC 18.0   | 27111701 |
| UNSPSC 19.0   | 27111701 |
| UNSPSC 20.0   | 27111701 |
| UNSPSC 21.0   | 27111701 |

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

|     |  |                          |
|-----|--|--------------------------|
| EAC |  | RU C-<br>DE.AI30.B.01750 |
|-----|--|--------------------------|

---

