

Side element - UM122-SEMFE-A92 - 2909442

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Lateral element, to attach profile cover UM 122 to DIN rail NS 35/7.5, with M3 screw fixture, tightening torque 0.25 Nm



Your advantages

- Inexpensive as a result of reducing the number of separate housing parts
- Wide range of options for external conductor connection
- Flexible size and shape
- High degree of mechanical stability by screwing the lateral elements to the profile
- Can be snapped onto standard NS 35/7,5 and NS 35/15 DIN rails



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 171681
GTIN	4017918171681
Weight per Piece (excluding packing)	28.800 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Product properties

Brief article description	Side element
Type	UM122-SEMFE-A92
Order No.	2909442
Housing type	Press-drawn section housings
Type	Lateral element

Dimensions

Depth [d]	127.5 mm
-------------	----------

Side element - UM122-SEMFE-A92 - 2909442

Technical data

Material specifications

Housing material	PA
Color (RAL)	green
Flammability rating according to UL 94	V0

Packaging specifications

Pieces per package	10
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501

Side element - UM122-SEMFE-A92 - 2909442

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

Approvals


Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC		B.01742
-----	---	---------