

PRODUCT-DETAILS

F204 AC-40/0,03

F204 AC-40/0,03 Residual Current Circuit Breaker



General Information

Extended Product Type	F204 AC-40/0,03
Product ID	2CSF204001R1400
EAN	8012542781301
Catalog Description	F204 AC-40/0,03 Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Technical

Standards	IEC/EN 61008 UL 1053
Operating Characteristic	Instantaneous
Type of Residual Current	AC type
Rated Residual Current	30 mA
Rated Current (I_n)	40 A
Number of Poles	4
Position of Neutral Terminals	Right
Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Voltage (U_r)	230/400 V
Rated Frequency (f)	50...60 Hz

Environmental

Ambient Air Temperature	Operation -25...55 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC
Short-Circuit Current Rating (SCCR)	0.03 mA

Dimensions

Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.360 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.082 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.403 kg
Package Level 1 EAN	8012542781301

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

Classifications

Object Classification	Q
-----------------------	---

Code	
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

