

PRODUCT-DETAILS

# DS204 AC-C16/0,03

## DS204 AC-C16/0,03 - RCBo



### General Information

Extended Product Type	DS204 AC-C16/0,03
Product ID	2CSR254001R1164
EAN	8012542873808
Catalog Description	DS204 AC-C16/0,03 - RCBo
Long Description	The RCBOs DS200 series has the function to protect against overload and short-circuit currents; protection against the effects of sinusoidal alternating earth fault currents; protection against indirect contacts and additional protection against direct contacts.

### Technical

Standards	IEC/EN 60947-2 IEC/EN 61009-1
Type of Residual Current	AC type
Number of Poles	4
Number of Protected Poles	4
Rated Current ( $I_n$ )	16 A
Rated Voltage ( $U_r$ )	400 V AC
Rated Short-Circuit Capacity ( $I_{cn}$ )	(400 V AC) 6 kA
Rated Ultimate Short-	(400 V AC) 10 kA

Circuit Breaking Capacity  
( $I_{cu}$ )

Tripping Characteristic	C
Electrical Endurance	10000 cycle
Connecting Capacity	Busbar 10 mm <sup>2</sup> Rigid 16 ...25 mm <sup>2</sup> Flexible 16 ...25 mm <sup>2</sup>
Power Supply Connection	Arbitrary
Position of Neutral Terminals	Right
Power Loss	6.6 W

---

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
-------------------------	----------------------------------------------------

---

## Technical UL/CSA

Short-Circuit Current Rating (SCCR)	30 mA
----------------------------------------	-------

---

## Dimensions

Product Net Width	105 mm
Product Net Height	0.093 m
Product Net Depth / Length	69 mm
Product Net Weight	0.780 kg

---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.49 m
Package Level 1 Height	0.11 m
Package Level 1 Depth / Length	0.09 m
Package Level 1 Gross Weight	0.83 kg
Package Level 1 EAN	8012542873808

---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5607
-----------------------------------	-----------------

Environmental Information	Refer to RoHS
Instructions and Manuals	9AKK107045A1451
RoHS Information	2CSC423002K2701

---

## Popular Downloads

---

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	9AKK107045A1451

---

## Classifications

---

Object Classification Code	Q
ETIM 4	EC002281 - Distributor assembly with combination RCCB/MCB
ETIM 5	EC002281 - Distributor assembly with combination RCCB/MCB
ETIM 6	EC002281 - Distributor assembly with combination RCCB/MCB
ETIM 7	EC002281 - Distributor assembly with combination RCCB/MCB

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

