

# Interchangeable Wall Plug Power Supply 5.1V DC 15.3 Watt

**multicomp** PRO

**RoHS  
Compliant**



## Features

- Interchangeable AC Heads
- Level VI Efficiency
- Worldwide Approvals

## Description

The 5.1V DC, 3 Amp interchangeable power supply with USB Type C output connector. The unit is finished in Black and comes complete with UK, Euro, USA and Auz AC Heads with all the relevant country approvals.

## Specifications

Input Voltage Range	90V AC to 264V AC
Input Frequency Range	47Hz to 63Hz
Input Current Rated	0.6A Max
Input AC Heads	UK, Euro, USA and Auz
Output Voltage Rating	+5.1V
Output Current Max	3A
Output Current Min	0A
Output Connection Type	Plug Type C
Total Output Regulation	±5%
Line Regulation	±2%
Ripple & Noise	240mVp-p
Efficiency	81.97% Min
Over Voltage Protection	10V DC maximum
Over Current Protection	5A maximum with auto-recovery function
Short-Circuit Protection	The adapter shall not be damaged by short the DC output to Ground
Operating Temperature	0°C to +40°C
Storage Temperature	20°C to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000V AC 10mA 1min
Leakage Current	0.25mA max
Warranty	12 Months
Safety Standard	UL/CUL(UL62368) TUV-GS(EN62368) SAA(AS/NZS62368)
EMI Standard	FCC(PART 15 CLASS B) CE(EN55032) RCM

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro




**multicomp** PRO

# Interchangeable Wall Plug Power Supply 5.1V DC 15.3 Watt

**multicomp** PRO

MTBF	50K Hours
Size (Max.)	74.5m (L) × 36mm (W) × 54mm(H)
Weight	115g ±15%

## Diagrams



Dimensions : Millimetres

## Part Number Table

Description	Part Number
Interchangeable Wall Plug Power Supply 5.1V DC 15.3 Watt	MP004971

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO