

USB-C to HDMI Adapter Cable, 4K 60Hz, HDCP 2.2, White, 3 ft.

MODEL NUMBER: **U444-003-H4K6WE**



USB-C to HDMI cable directly connects an HDMI monitor to your tablet, MacBook, Chromebook or smartphone's USB-C or Thunderbolt 3 port.

Features

USB-C to HDMI Adapter Connects to Your Computer's USB-C or Thunderbolt 3 Port This USB Type-C to HDMI adapter (M/M) connects an HDMI monitor, projector or television to the USB-C or Thunderbolt 3 port on your desktop computer, tablet, laptop, notebook, MacBook, Chromebook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger 4K screen. No other adapter or cable is needed to complete your 4K connection.

Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals By connecting the USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

Enjoy the Clarity of True 4K HDMI Video with Multi-Channel Audio and 4:4:4 Color This 4K HDMI cable supports Ultra HD video resolutions up to 4096 x 2160 (4K x 2K) at 60 Hz for crystal-clear picture and sound. It's compatible with HDCP 2.2 and HDMI 2.0 standards for carrying HDR (high dynamic range) signals. It also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as 36-bit Deep Color (12 bits per channel).

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB Type-C to HDMI cable requires no software or external power. Just connect the USB-C plug to the USB-C or Thunderbolt 3 port on a source device that supports USB DisplayPort Alternate Mode, and connect the HDMI plug to your display. The three-foot USB 3.1 Gen 1 cable is backward compatible with previous USB and HDMI generations, so you can use it with legacy equipment.

Highlights

- Converts audio/video signals from sources supporting USB DisplayPort Alt Mode
- Delivers Ultra HD picture quality at resolutions up to 4096 x 2160 (4K) @ 60 Hz
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Compatible with latest HDMI standards, including 4:4:4 subsampling for HDR televisions
- Dual male plugs connect directly to devices—no other adapter or cable is needed
- Note: This cable is unidirectional. Will only work from a USB-C port to HDMI port

Applications

- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Attach an HDTV to your PC for use as a 4K monitor

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode



- Display device with HDMI input

Package Includes

- U444-003-H4K6WE USB-C to HDMI Adapter, M/M, White, 3 ft.

Specifications

OVERVIEW	
UPC Code	037332238245
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
Bus Powered	Yes
BATTERY	
Battery Charging (1.2 Port)	No
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5mm
Color	White
Material of Construction	PVC and ABS
Unit Packaging Type	Polybag
Unit Weight (kg)	0.07
Unit Weight (lbs.)	0.15
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.1 BTU/Hr
Power Consumption (Watts)	0.6
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	



Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	HDMI: 3840 X 2160, Including 4096 x 2160, (4K X 2K) @ 60HZ
HDMI Specification	2.0
HDCP Specification	2.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Max Supported Color Depth	36-bit Deep Color
Technology	HDMI; USB; USB 3.1 (Gen 1)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>