



MASTER TL5 High Output

MASTER TL5 HO 54W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [Not Applicable]
System Description	High Output
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	5000 lm
Luminous Flux (Rated) (Nom)	4500 lm
Color Designation	Warm White (WW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	93 lm/W
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	83 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	85
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	54.1 W
Lamp Current (Nom)	0.455 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

MASTER TL5 High Output

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Cap-Base Information Green Plate

Approval and Application

Energy Efficiency Label (EEL) A+

Mercury (Hg) Content (Nom) 1.4 mg

Energy Consumption kWh/1000 h 59 kWh

Product Data

Full product code 871150064316255

Order product name MASTER TL5 HO 54W/830 SLV/40

EAN/UPC - Product 8711500643162

Order code 927929083055

Numerator - Quantity Per Pack 1


Numerator - Packs per outer box 40

Material Nr. (12NC) 927929083055

Net Weight (Piece) 105.800 g

ILCOS Code FDH-54/30/1B-L/P-G5-16/1150

Dimensional drawing




Product


MASTER TL5 HO 54W/830 SLV/40

TL5 HO 54W/830

Photometric data



LDPB_TL5-HO8_830-Spectral power distribution B/W



LDPO_TL5-HO8_830-Spectral power distribution Colour

MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

