

# Professional Series

## VELCRO® Brand Universal Flooring Fastener

### HTH 830 / PS Removable



**VELCRO® Brand Extruded High Technology Hook, Low profile for indoor use.**

Adhesive designed for a wide number of substrates such as aluminum, stainless steel, glass, plywood, polyester, PVC-Vinyl and Concrete. Adhesive is not suitable for polyethylene, polypropylene and Fabrics

High adhesive temperature resistance - Low tack adhesion - Residual Free.

- **Width:** 45 and 107mm
- **Length:** 25 meters
- **Colour:** White
- **Material:** Polypropylene
- **Adhesive temperature ranges:** -40°C to +140°C

For Applications where medium cycling is required.

#### ADHESIVE SUBSTRATE COMPATIBILITY

Aluminium Adonized	✓
Glass	✓
Painted Wallboard	✓
Plywood	✓
Polyester	✓
Polyethylene	✗
Polypropylene	✗
Stainless Steel	✓
Vinyl	✓
Formica (Polished Side)	✓
Cardboard	✓
Polyacrylic	✓
Fabrics	✓

✓ Recommended    ✓ Good    ✗ Not Recommended

#### Part Numbers

- **VEL-PS20021** = 45mm wide White – 25 meters
- **VEL-PS20027** = 107mm wide White – 25 meters



Education



OEM



Oil & Gas



Energy & Utility



Finance



Government



Health Care







Manufacturing

**TYPICAL SYSTEM PERFORMANCE**

The following information should be considered typical and is intended to be used as a reference only. This information should not be used for specification purposes. Suitable performance for the specific intended application should be evaluated by the user.

Unless Otherwise stated tests were performed under controlled nominal laboratory conditions of 23°C (72°F) and 50% Relative Humidity. General Storage conditions: 18 - 24°C (65-75°F) with Relative Humidity of 40 to 65%.

**PERFORMANCE CHARACTERISTICS**

Fastener	VELCRO® Brand High Technology Hook HTH 830
 <b>Closure Peel Strength</b>	Avg. = # N/cm *Dependent on the flooring backing
 <b>Closure Shear Strength</b>	Avg. = # N/cm <sup>2</sup> *Dependent on the flooring backing
 <b>Tensile Disengagement</b>	Avg. = # N/cm <sup>2</sup> *Dependent on the flooring backing
 <b>Cycle Life</b>	*Dependent on the flooring backing

\* Average based on recorded values. The specifications are for reference.

**ATTACHMENT TECHNIQUE**

Adhesive PS Removable should be applied with even pressure, ensuring good contact is made with the substrate. As with all VELCRO® Brand adhesives, the substrate must be free of grease, moisture, dust, silicones, etc. and should be cleaned with alcohol and fully dried prior to application of the adhesive.

**CHARACTERISTICS**

**Shelf Life:** Adhesive PS Removable has a shelf life of 2 years from the production date. Keep cool, dry and protect from sunlight. For performance characteristics of the adhesive, refer to the PS Removable technical data sheet.

**SPECIAL CHARACTERISTICS**



**Outdoor use**

Since the product is made with polypropylene has a tendency to degrade and have low resistance to UV rays. As a result, the **VELCRO® Brand Extruded High Technology Hook** is not recommended for outdoor use and for direct, prolonged exposure to UV light.



**Resistance to solvents**

Polypropylene in this fastening system is resistant to cleaning with some solvents and to accidental exposure to the most common solvents; however, certain fluids used in transport, such as gasoline, motor oil or transmission fluids can cause degradation, particularly over long periods of time and at elevated temperatures. The product should be tested in use for a specific application.



**Fire resistance**

**VELCRO® Brand Extruded High Technology Hook** does not have a flame-retardant treatment, so their use in applications that require limited flame propagation is not recommended.



**Water/Moisture resistance**

**VELCRO® Brand Extruded High Technology Hook** can lose its properties if it comes in contact with water, and thus washing the material is not recommended.



**Electrostatic discharge**

**VELCRO® Brand Extruded High Technology Hook** has not been tested for electrostatic discharge after opening and closing the fastener. These products must first be tested in applications where electrostatic discharge is a concern.

---

## REGULATORY ELEMENTS

For product declarations of conformity on regulatory elements and additional information, contact [productcompliance\\_emea@velcro.com](mailto:productcompliance_emea@velcro.com).

---

## PRODUCT USE

The information, statements and comments contained within this document are based on our experience and testing and are believed to be accurate. However, because there are many factors involved in specific applications that can impact end use and performance, product users should always test the product for its ability to meet the requirements of their specific use and method of application.

---

## LIMITED WARRANTY

Velcro Companies<sup>(\*)</sup> warrants that all of its products will substantially comply with its written specifications at the time of shipment. ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY DISCLAIMED. The product user is responsible for determining whether the product is fit and suitable for the intended application. If the product does not meet specifications as warranted, we will, at our option, repair or replace the product, or credit or refund the purchase price. The foregoing constitutes the user's sole remedy and our sole obligation hereunder.

(\*) Velcro Companies includes all the partner companies involved in the development, manufacture or sale of the products.

---

## LIMITATION OF LIABILITY

To the maximum extent permitted under applicable law, our liability for any losses or damages relating to use of the product shall not exceed the purchase price for such product, regardless of whether such losses or damages are direct, indirect, special, incidental or consequential, and regardless of the legal theory asserted, including, but not limited to, warranty, contract, negligence or strict liability.

Given the diversity of our products, we recommend that our customers verify that the product satisfies the requirements of their application. The customer is responsible for the application and use of the product.

### GLOBAL OFFICES

#### Global Corporate Headquarters

Velcro USA Inc.  
95 Sundial Avenue  
Manchester, NH 03103  
USA  
Tel: (+1) 800 225 0180  
[marketing@velcro.com](mailto:marketing@velcro.com)  
Velcro.com

### NAM

#### USA

Velcro USA Inc.  
Tel: (+1) 800 225 0180  
[marketing@velcro.com](mailto:marketing@velcro.com)  
Velcro.com

#### Canada

Velcro Canada Inc.  
Tel: (+1) 800 683 5276  
[canada@velcro.com](mailto:canada@velcro.com)  
Velcro.com

### LATAM

#### Mexico

Velcro de México, S.A. de C.V.  
Tlalnepantla de Baz,  
Edo. de México  
Tel: (+52) 55 5005 3300  
[infovdmex@velcro.com](mailto:infovdmex@velcro.com)  
Velcrodemexico.com  
León, Gto  
Tel: (+52) 477 980 0630  
[infovdmex@velcro.com](mailto:infovdmex@velcro.com)  
Velcrodemexico.com

#### Brazil

Velcro Brasil Importação,  
Exportação e Comércio de  
Sistemas de Fixação Ltda.

Campo Bom, RS  
Tel: (+55) 51 3599 1483  
[infovbra@velcro.com](mailto:infovbra@velcro.com)  
Velcro.com.br

Sumaré, SP  
Tel: (+55) 11 3197 2588  
[infovbra@velcro.com](mailto:infovbra@velcro.com)  
Velcro.com.br

#### Uruguay

Velcro Industrial  
del Uruguay S.A.  
Tel: (+598) 2288 0008  
[infovurg@velcro.com](mailto:infovurg@velcro.com)  
Velcro.com

### EMEA

#### Spain

Velcro Europe S.A.  
Tel: (+34) 93 758 32 98  
[infovesa@velcro.com](mailto:infovesa@velcro.com)  
Velcro.es

#### Germany

Velcro GmbH  
Tel: (+49) 7141 991 19-0  
[infovgmh@velcro.com](mailto:infovgmh@velcro.com)  
Velcro.de

#### France

Velcro Industries France S.A.S.  
Tel: (+33) 1 34 38 78 88  
[infovif@velcro.com](mailto:infovif@velcro.com)  
Velcro.fr

#### Belgium

Alfatex N.V.  
Tel: (+32) 9 386 12 18  
[infofeb@velcro.com](mailto:infofeb@velcro.com)  
Velcro.be

#### Italy

Velcro Italia, S.R.L.  
Tel: (+39) 039 62 70 01  
[infoveit@velcro.com](mailto:infoveit@velcro.com)  
Velcro.it

#### UK

Velcro Ltd.  
Tel: (+44) 1606 738 806  
[infovtd@velcro.com](mailto:infovtd@velcro.com)  
Velcro.co.uk

#### Poland

Velcro Poland Sp. z o.o.  
Tel: (+48) 71 798 57 89  
[infovpl@velcro.com](mailto:infovpl@velcro.com)  
Velcro.pl

### APAC

#### Australia

Velcro Australia Pty. Ltd.  
Tel: (+61) 3 9703 2466  
[infovaus@velcro.com](mailto:infovaus@velcro.com)  
Velcro.com.au

#### China

Velcro China Fastening  
Systems Company Limited  
Tel: (+86) 512 8164 5888  
[infovch@velcro.com](mailto:infovch@velcro.com)  
Velcro.com.cn

#### Hong Kong

Velcro Hong Kong Ltd.  
Tel: (+852) 2570 3698  
[infovhk@velcro.com](mailto:infovhk@velcro.com)  
Velcro.com.hk

#### Vietnam

Velcro Vietnam Company Limited  
Tel: (+84) 274 2222 497  
[infovnm@velcro.com](mailto:infovnm@velcro.com)  
Velcro.com

VELCRO® and other brands are owned by Velcro BVBA © 2019