


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2004711002](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Single Row, UL 94V-0, Glow-Wire Capable, 2 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2004710001-PK-000 (PDF)</a>
<a href="#">Product Specification 2029880002-PS-000 (PDF)</a>	<a href="#">Test Summary 2131370002-TS-000 (PDF)</a>
<a href="#">Product Specification 2131370000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2131370000-AS-000 (PDF)</a>	



**General**

Product Family	Crimp Housings
Series	<a href="#">200471</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Product Name	Mini-Fit Sigma
UPC	193264446209

**Physical**

Circuits (maximum)	2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.000/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2131370000-AS-000
Packaging Specification	2004710001-PK-000
Product Specification	2029880002-PS-000, 2131370000-PS-000
Sales Drawing	2004710001-SD-000
Test Summary	2131370002-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[200471 Series](#)

**Mates With**

Mini-Fit Sigma Receptacle Housing  
[2004531002](#)

**Use With**

Mini-Fit TPA2/Sigma Male Terminal  
[172765](#) , [203070](#) . Mini-Fit Sigma Retainer  
[1727092002](#)