



## Beyond the Limit

### microSDXC/SDHC UHS-I U1 Class 10

#### Unparalleled Experience of Speed

U1 Class 10 delivers up to 80/20MB/s in read/write that outpaces its competitors by a huge margin. The random performance of Apacer's memory card also tops its class, offering the smoothest user experience when checking status updates on Facebook, taking & browsing photos, recording videos, surfing the web, navigating on maps or playing games.

\*Transmission speeds vary based on your system performance (e.g. hardware, software, usage, etc.)

#### Memory Capacity

Storage size of the card



#### Speed Class


The minimum guaranteed write speed when used with a device that does not support UHS-I interface.

#### UHS Speed Class

The minimum guaranteed write speed when used with devices that support the UHS-I interface.

#### UHS-I

This indicates that the card is supported by the UHS-I interface



#### Ultra high 128GB capacity

Apacer's newest microSDXC UHS-I U1 memory card has a storage capacity of 128 GB, allowing it to accommodate 32,000 JPG photographs and 45.6 hours of 720p HD videos.

#### Outstanding Performance

MicroSDXC UHS-I U1 memory card quickly responds to each operation of users. Whether you use Facebook, take photos, record videos, view albums, surf the Internet, navigate maps or play games, it can bring you smooth and consummate user experience.

Capacity	4GB	8GB	16GB	32GB	64GB	128GB
Picture(6MP) [1]	2432	4846	9728	19456	38912	77824
Picture(8MP) [1]	2048	4096	8192	16384	32768	65536
Picture(10MP) [1]	1769	3537	7075	14150	28300	56599
Picture(12MP) [1]	1556	3113	6226	12452	24904	49807
Video(QCIF) [2]	90	182	364	730	1460	2922
Video HD [2]	10	20	40	88	178	357
Audio [3]	1037	2074	4150	8300	16601	33204

[1] The numbers of image are based on a JPEG format image; this will vary from the camera model and settings.

[2] Actual recording time will vary from the camera model, resolution, compression settings and content being recorded.

[3] The numbers of song will vary from the compression rate and device.

## Green design! Do something for Earth

Apacer' full series of memory cards meet EU's RoHS environmental directive by adopting lead-free process for production which does not cause any environmental pollution, and it protect Earth with you!



## Features

- Compliant with latest SD spec ver 3.0
- Supports UHS-I specification
- Safeguards valuable data with multiple protection

## Specification

- Capacity: 8GB / 16GB / 32GB / 64GB / 128GB
- Performance: UHS Speed: Class 1  
Speed Class: Class 10
- Dimensions (L x W x H): 15 x 11 x 1mm
- Warranty: Limited product lifetime

## Ordering Information

Capacity	PN	EAN Code
8GB*	AP8GMCSH10U1-R	4712389898852
16GB*	AP16GMCSH10U1-R	4712389898869
32GB*	AP32GMCSH10U1-R	4712389898876
64GB*	AP64GMCSX10U1-R	4712389898883
128GB*	AP128GMCSX10U1-R	4712389911049

\* With Adapter



## Apacer Technology Inc.

1F, No.32, Zhongcheng Rd., Tucheng Dist.  
New Taipei City 236, Taiwan R.O.C.  
Tel: +886-2-2267-8000  
Fax: +886-2267-3410