

# Decorative LED candles and lusters

## Classic LEDCandle D 5-32W BA35 E14 822 GOLD

The new Deco collection (candles and lusters) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Light Technical	
Color Code	822 [ CCT of 2200K]
Luminous Flux (Nom)	350 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	5 W
Lamp Current (Nom)	38 mA


Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh

# Decorative LED candles and lusters

Product Data	
Full product code	871869681443700
Order product name	Classic LEDCandle D 5-32W BA35 E14 822 GOLD
EAN/UPC - Product	8718696814437
Order code	929001896502

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001896502
Net Weight (Piece)	0.024 kg


## Dimensional drawing




Candle BA35 230V 4.5-32W 350lm 2000K E27

Product	D	C
Classic LEDCandle D 5-32W BA35 E14 822 GOLD	35 mm	129 mm


## Photometric data



LED Bulb CLA 8-50W E27 ST64 Amber 822 DIM




LED Candle CLA 5-32W E14B A35 Amber 822 DIM




LED Candle CLA 5-32W E14 B35 Amber 822 DIM

## Decorative LED candles and lusters

### Lifetime



LEDBulb CLA 5.5-40W E27 ST64 Clear 827 DIM



LEDBulb CLA 5.5-40W E27 ST64 Clear 827 DIM

