

# Technical data sheet · Cablefix® Vario

## Feed-through for all prefabricated cables and wires with connectors



Cable fittings and accessories

<b>Identification</b>	Type	BL6
	Part-No.	606252
<b>Use/Area of application</b>		
Application	<ul style="list-style-type: none"><li>• Electrotechnology, pneumatics, hydraulics, robotics, general machine and plant construction</li></ul>	
Properties	<ul style="list-style-type: none"><li>• Feed through and terminal frames from high-quality solid</li><li>• Aluminium or polyamide GF30 with additional inner brass reinforcement</li><li>• High flexibility in the application</li><li>• Additional mounting to existing installation easily possible</li><li>• Even pressure effect on the feed through round material yields good strain relief and sealing</li><li>• Unneeded holes in the module can simply sealed with blank plugs</li><li>• Compact design i.e. space-saving</li><li>• 2 module sizes with slot and suspension principle</li><li>• Very good weathering resistance</li><li>• Resistant to UV radiation, ozone, oils, fuels, acids, bases, solvents and sea water</li></ul>	
<b>Technical data</b>		
Burning behaviour	Flame-retardant	
Temperature range	-40 °C to +135 °C	
Protection class	IP 65	

10.05.2007 – Subject to technical modification

Part-No. 606252

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1-704-504-02 22 • Fax +1-704-504-02 23

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 4, Brabazon Court • Borman

Lichfield Road Industrial Estate • GB-Tamworth, Staffordshire B79 7TA

Tel. +44-18 27-3 13 33-0 • Fax +44-18 27-3 13 33-2

www.lutze.com • sales.gb@lutze.co.uk



Systematic Technology

# Technical data sheet · Cablefix® Vario

## Feed-through for all prefabricated cables and wires with connectors

---

Module type	VG=40×43.5 VK=40×22.9 for cable and wire diameters from 4 mm to 34.5 mm, see ordering information frame sizes, see ordering information
Maße (L×H×T)	30
Diameter	6.0

---

### Design

Length	30.00 mm
--------	----------

---

### General data

VE	50 piece
suitable for Part-No.	606153
Note	Unit corresponds to the number of required rubber modules type VK or VG

10.05.2007 – Subject to technical modification

Part-No. 606252

USA: LUTZE INC.

13330 South Ridge Drive · Charlotte, NC 28273, USA

Tel. +1-704-504-02 22 · Fax +1-704-504-02 23

www.lutze.com · info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 4, Brabazon Court · Borman

Lichfield Road Industrial Estate · GB-Tamworth, Staffordshire B79 7TA

Tel. +44-18 27-3 13 33-0 · Fax +44-18 27-3 13 33-2

www.lutze.com · sales.gb@lutze.co.uk



**Systematic Technology**