

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347910141](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Receptacle, Single Row, Bridged, 4 Circuits, Polarization Option B, Gray

Documents:

3D Model	Application Specification AS-34791-020-CH-001 (PDF)
3D Model (PDF)	Application Specification AS-34791-020-FR-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-538-001 (PDF)
Product Specification PS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34791-020-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	34791
Application	Automotive, Power, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	B
Product Name	Mini50
UPC	887191319803

Physical

Circuits (maximum)	4
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.787/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-538-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34791-001-000, SD-34824-003-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[34791 Series](#)

Mates With

Mini50 Vertical Header [34792](#) , Mini50 Right-Angle Through Hole Header [34793](#) , Mini50 Right-Angle Surface Mount Header [34912](#)

Use With

CTX50 Unsealed Terminals [560023](#)