

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2170640061](#)  
**Status:** **Active**  
**Overview:** [Micro-One Wire-to-Board Connector System](#)  
**Description:** Micro-One Wire-to-Board Header, Right-Angle, 2.00mm Pitch, Single Row, Glow-Wire Capable, 6 Circuits, Tin-Bismuth Plating, Black

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification 2170649200-SPK-200 \(PDF\)](#)  
[Product Specification 2059790000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification 2059790000-AS-000 \(PDF\)](#)

**General**

Product Family	PCB Headers
Series	<a href="#">217064</a>
Application	Power, Wire-to-Board
Overview	<a href="#">Micro-One Wire-to-Board Connector System</a>
Product Name	Micro-One
UPC	195842005624

**Physical**

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	1098.363/mg
Number of Rows	1
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount


**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2059790000-AS-000
Packaging Specification	2170649200-SPK-200
Product Specification	2059790000-PS-000
Sales Drawing	2170640000-SD-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[217064](#) Series

**Mates With**

Micro-One Receptacle Housing [205979](#)