

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → End Stops

## General Information

<b>Extended Product Type:</b>	BAH22
<b>Product ID:</b>	1SNA164655R0400
<b>EAN:</b>	3472591646559
<b>Catalog Description:</b>	BAH22 End Stops
<b>Long Description:</b>	BAH22 End Stops - - 7.1mm Spacing.

## Ordering

<b>Color:</b>	Grey
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85369010

## Dimensions

<b>Product Net Width:</b>	7.1 mm
<b>Product Net Height:</b>	30 mm
<b>Product Net Depth / Length:</b>	18 mm
<b>Product Net Weight:</b>	10 g

## Technical

<b>Spacing:</b>	8.2 mm
<b>Function:</b>	End Stops
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461
<b>Suitable For:</b>	HD10/12.F5 HD10/12.FF5 HD16/14.FF5 HD35/16.F6 HD4/10.F4.19 HD4/9.F4 HD6/22.F12G HD6/30.F12G

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

<b>RoHS Information:</b>	1SND230479F0206
--------------------------	-----------------

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC001041 - End bracket for terminal block
<b>ETIM 5:</b>	EC001041 - End bracket for terminal block
<b>ETIM 6:</b>	EC001041 - End bracket for terminal block

## Container Information

<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	155 mm
<b>Package Level 1 Depth / Length:</b>	200 mm
<b>Package Level 1 Height:</b>	5 mm
<b>Package Level 1 Gross Weight:</b>	0.5 kg
<b>Package Level 1 EAN:</b>	3472591646559
<b>Package Level 2 Units:</b>	1000 piece
<b>Package Level 2 Width:</b>	175 mm
<b>Package Level 2 Depth / Length:</b>	227 mm
<b>Package Level 2 Height:</b>	260 mm
<b>Package Level 3 Units:</b>	80000 piece
<b>Product Packing Type:</b>	Bag

