

MEDICAL WALL MOUNT INTERCHANGEABLE BLADE POWER SUPPLY 24VDC 24 WATT



STONTRONICS: UES24LCP-240100SPA

Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals

Description:

Our range of 24 Watt Medical Interchangeable wall plug power supplies provide 24 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro, USA & Aus AC Heads , all Efficiency Level VI and carry worldwide safety approvals.

Specification	
Part Code	y - o G#h ch°
Input Voltage Range	90-264 Vac
Input Frequency Range	50-63Hz
Input Current Rated	0.1A Max
Input AC Heads	UK, Euro, USA & Aus
Output Voltage Rating	+24V
Output Current Range	1A
Output Min Current	0A
Output Connection Type	2.1x5.5x12 mm centre positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	240mVp-p
Efficiency	87% Min
Over Voltage Protection	Auto Recovery
Over Load Protection	0.55-0.9 A maximum with auto-recovery function
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +60°C
Operating Humidity	20% to 85%
Storage Humidity	5% to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	CB, UL, TUV, RCM
EMI Standard	Meets CE(EN55022)
MTBF	50K Hours
Size mm max.	88(L) x 30(W) x 57(H) (Without AC Head)
Weight	170 g

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

STONTRONICS


TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

MEDICAL WALL MOUNT INTERCHANGEABLE BLADE POWER SUPPLY 24VDC 24 WATT



STONTRONICS: UES24LCP-240100SPA

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

STONTRONICS

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500