

PBBOX Push button plastic boxes



PBBOX3HBY

- Pre-cut cable inlet PG13.5/M20
- UL approved plastic material
- Black base and yellow or grey cover
- From 1 to 5 holes
- CE

Product Description

These boxes, made by UL approved ABS plastic material, are ideal for push buttons application like push button station, emergency STOP push button box, start-stop box etc... They are available from 1 to 5 holes that are fitted for 22mm push buttons series. The black base has a pre-pressed cable inlet type Pg (Pg13.5) or Metric (M20). The cover is available either yellow or grey colours.

Ordering Key

PBBOX 3H BY *

Model _____
 Number of Holes _____
 Box Colour _____

* Not all configurations available – see page 3 for complete list

Approvals



General Data

Material	ABS PA-765
Weight	1H 80g / 2.82oz 2H 100g / 3.53oz 3H 120g / 4.23oz 4H 160g / 5.64oz 5H 180g / 6.35oz
Hole diameter	Ø22mm / 0.87"
Operating temperature	-40°C...+60°C / -40°F...+140°F
Degree of protection	IP00


Number of holes

1H	1 hole
2H	2 holes
3H	3 holes
4H	4 holes
5H	5 holes



Box Colours

BY	Base: Black Cover: Pantone Yellow
BG	Base: Black Cover: Grey RAL7035

Dimensions (mm/inches)



Dimensions (mm/inches)



AVAILABLE PORTFOLIO CONFIGURATIONS

Flush Round Push Buttons		Pilot Lights		I/O Push Buttons	
PB22BF0B	PB22BIF0Y	PL22CHLB110	PL22SFLG24	PB22SIO0RG	PB22SIOL0RG
PB22BF0G	PB22SF0B	PL22CHLB24	PL22SFLR110	Key Selector Switches	
PB22BF0K	PB22SF0G	PL22CHLG110	PL22SFLR24		
PB22BF0R	PB22SF0K	PL22CHLG24	PL22SFLW110	PB22SKRS21KL PB22SKRS21KR	
PB22BF0W	PB22SF0R	PL22CHLR110	PL22SFLW24	Push Button Boxes	
PB22BF0Y	PB22SF0Y	PL22CHLR24	PL22SFLY110		
PB22BIF0B	PB22SIF0G	PL22CHLW110	PL22SFLY24	PBBOX1HBG	PBBOX3HBY
PB22BIF0G	PB22SIF0R	PL22CHLW24	PL22SHLG110	PBBOX1HBY	PBBOX4HBG
PB22BIF0R	PB22SIF1G	PL22CHLY110	PL22SHLG220A	PBBOX2HBG	PBBOX4HBY
PB22BIF0W		PL22CHLY24	PL22SHLG24	PBBOX2HBY	PBBOX5HBG
		PL22CLLB220A	PL22SHLR110	PBBOX3HBG	
		PL22CLLB24	PL22SHLR12	Lamp Element	
		PL22CLLG110	PL22SHLR220A		
Extended Push Buttons		PL22CLLG220A	PL22SHLR24	PALAMPB110	PALAMPR24
PB22BE0G	PB22BIE0Y	PL22CLLG24	PL22SHLW110	PALAMPB24	PALAMPW110
PB22BE0K	PB22SIE0G	PL22CLLR110	PL22SHLW24	PALAMPG110	PALAMPW12
PB22BE0R	PB22SIE0R	PL22CLLR220A	PL22SHLY110	PALAMPG220A	PALAMPW24
PB22BIE0R		PL22CLLR24	PL22SHLY24	PALAMPG24	PALAMPY110
Red Emergency Stop Push Buttons		PL22CLLW110	PL22SLLG110	PALAMPR110	PALAMPY24
		PL22CLLW220A	PL22SLLG220A	PALAMPR220A	
PB22BEM41R	PB22SEM41R	PL22CLLW24	PL22SLLG24	Contact Block	
PB22BEM61R	PB22SEM61R	PL22CLLY110	PL22SLLR110		
PB22BKEM41R		PL22CLLY12	PL22SLLR220A	PA2010/1	PA2100/2
Mushroom Push Buttons		PL22CLLY220A	PL22SLLR24	PA2010/2	PA2110/1
		PL22CLLY24	PL22SLLW24	PA2020/1	PA2110/2
PB22BIM41R	PB22SM40K	PL22CRLB24	PL22SLLY24	PA2020/2	PA2200/1
PB22BM40G	PB22SM40R	PL22SFLB24	PL22SRLR110	PA2100/1	PA2200/2
PB22BM40R	PB22SM41G	PL22SFLG110		Accessories	
PB22BM41R	PB22SM41R				
PB22BM60R	PB22SPPM41R	Short-Handle Selector Switches		PASEALCOV	PAWP6
PB22BM60R	PB22SPPM61R	PB22BSRS21K	PB22SISRS21W	PAPBCOV	PAWP9
PB22SIM40R	PB22SPPM61R	PB22BSRS22K	PB22SISRS31G	PAMR22	PAPHC22
PB22SIM41R		PB22BSRS31K	PB22SSRS21K	PALBF11	PARR3
Buzzer and Flashing Buzzer		PB22BSRS33K	PB22SSRS31K	PALBF18	PAPLCONN
		PB22SISRS21R	PB22SSRS32K	Holders	
PL22SBZK110	PL22SFBZR110	Long-Handle Selector Switches			
PL22SBZK12	PL22SFBZR12	PB22BLRS21K	PB22SLRS31K	PBMBN	
PL22SBZK220A	PL22SFBZR220A	PB22BLRS31K	PB22SLRS32K		
PL22SBZK24	PL22SFBZR24	PB22BLRS21K			
Two Color Pilot Lights					
		PL22STCRG110	PL22STCRG24		
PL22STCRG220A					