

Two, Four and Eight Port RS232 to USB Adaptors



OMG-USB-232-4, shown smaller than actual size.

OMG-USB-232-2 Series



- ✓ Power Obtained from USB Cable - No External Power Required
- ✓ "Hot swapping"/ Auto Configuration
- ✓ High Speed UART with 128 byte TX FIFO and 384 byte RX
- ✓ FIFO Supporting Standard PC Data Rates up to 460.8K bps
- ✓ 1.8 M (6') High Quality USB Cable Provided
- ✓ Includes Driver and Utility Software

The OMG-USB-232 USB to serial I/O adaptors provide two, four or eight RS-232 serial ports for USB connectivity to legacy or non-USB compliant devices. OMB-USB-232 adaptors support standard PC data rates up to 460K bps.

Simply install the included software and connect the OMB-USB-232 adaptor to your USB port. The device is immediately recognized by the system. At that point, simply connect the adaptor to your target device (i.e. modem, serial printer, scale, bar code/mag stripe reader, etc.).

Now your non-USB peripherals can have the same connection simplicity and ease of use as USB aware peripherals. We include our Windows 98/ME/2000/XP and Linux drivers to simplify installation.

Specifications

Number of Ports: 2, 4 or 8

Max. Data Rate: 460K

Max. Data Distance: up to 15 m (50')

Operating Temperature: 0 to 50°C (32 to 122°F)

Storage Temperature: -50 to 105°C (-58 to 221°F)

Humidity Range: 10 to 90% RH non-condensing

Power: USB cable

Connector(s): 2, 4 or 8 DB9P (male)

Dimensions:

OMG-USB-232-2, -4;

17.78 L x 13.34 W x 3.81 cm H (7.0 x 5.25 x 1.5"):

OMG-USB-232-8;

22.1 L x 15.5 W x 5.1 cm H (8.7 x 6.1 x 2.0")



OMG-USB-232-2, shown smaller than actual size.



OMG-USB-232-4, shown smaller than actual size.



OMG-USB-232-8, shown smaller than actual size.



OMG-CA179 USB cable, and software CD shown smaller than actual size

To Order	
Model Number	Description
OMG-USB-232-2	2 port RS232 to USB adaptor
OMG-USB-232-4	4 port RS232 to USB adaptor
OMG-USB-232-8	8 port RS232 to USB adaptor
OMG-CA177	DB9F/25M 1.8 m (6') cable
OMG-CA179	1.8 m (6') USB A to B cable
OMG-DR102	DIN rail mounting kit

All **OMG-USB-232** converters include utility software and a complete user's manual on CD-ROM and an **OMG-CA179** USB cable.
Ordering example: **OMG-USB-232-2** 2 port RS-232 to USB adaptor.