

Product information

97 90 22

Crimp Assortment

For cable connectors

- With Automatic Insulation Stripper KNIPEX Multistrip 10 (12 42 195)
- With crimping pliers KNIPEX PreciForce® 97 52 36 (for insulated terminals and plug connectors)
- In a TANOS MINI-systainer® (solid plastic box)
- T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®
- Opening when connected: fast and simple access to content without disconnecting
- Two stackable plastic inserts with 6 trays each for connectors
- With an assortment of standard cable connectors




General

Article No.	97 90 22
EAN	4003773062141
Weight	1,527 g
Dimensions	170 x 68 mm
Reach	yes
RohS	no

Classification

eCl@ss 5.1.4	27400218
ETIM 5.0	EC000524
ETIM 6.0	EC000524
proficl@ss 6.0	EAB559c013
UNSPSC 13.1	27112147

Content

12 42 195	1 x KNIPEX MultiStrip 10 Automatic Insulation Stripper (0,03 – 10,0 mm ²) MM
97 52 36	1 x KNIPEX PreciForce® Crimping Pliers (0,5 – 6,0 mm ²) MM 
	25 x Butt Connectors, insulated Yellow (25 x 4,0-6,0 mm ²)
	25 x Butt Connectors, insulated Blue (25 x 1,5-2,5 mm ²)
	25 x Butt Connectors, insulated Red (25 x 0,5-1 mm ²)
	25 x Cable Connectors, eye type Ø 6 mm (25 x 1,5-2,5 mm ²)
	25 x Cable Connectors, eye type Ø 5 mm (25 x 1,5-2,5 mm ²)
	25 x Cable Connectors, eye type Ø 4 mm (1,5-2,5 mm ²)
	25 x Cable Connectors, eye type Ø 5 mm (25 x 0,5-1 mm ²)

Content

	25 x Cable Connectors, eye type Ø 4 mm (25 x 0,5-1 mm ²)
	25 x Blade Terminal Sockets 6,3x0,8 mm (25 x 1,5-2,5 mm ²)
	25 x Blade Terminal Sockets 6,3x0,8 mm (25 x 0,5-1 mm ²)
	25 x Cable Connectors, eye type Ø 6 mm (25 x 4,0-6,0 mm ²)
	25 x Cable Connectors, eye type Ø 8 mm (25 x 4,0-6,0 mm ²)

technical change and errors excepted

Systemer® is a registered trademark of TANOS GmbH

