



Product # or Keyword



Silicone, 10 AWG, "Coolflex 45" Wire, White, 25'

[Home](#) ▶ [Products](#) ▶ [Wire/Cable](#) ▶ [Silicone, 10 AWG, "Coolflex 45" Wire, White, 25'](#)



ASK A QUESTION

Description

The WI-M-10-25 is a 25' section of Mueller's "Coolflex 45" wire that is 10 AWG, 1064 strand 56/08x19C, tinned copper wire with a highly flexible 0.197" (5mm)

diameter silicone jacket.

Model #: WI-M-10-25-9

Category: Wire/Cable

Weight: 495 g

Dimensions: 300" (L)

Data Files:

[DS-WI-M-10-@.pdf](#)

Product Details

Wire Gauge (AWG)

10

Color

White

Amps

45

Material

Tinned Copper

Wire Insulation Material

Silicone

UL Rating

UL758

Inventory & Distributors

Distributor Inventory: 2

[Check Distributor Inventory and Pricing](#)

Related Products



**Silicone, 10 AWG,
"Coolflex 45" Wire, White,
10'
WT-M-10-10-9**



**Silicone, 10 AWG,
"Coolflex 45" Wire, White
(per foot)
WT-M-10-9**

Connect with us on social media



Sign up for our newsletter

Sign Up

Products & Services

[View all products](#)

[Product Search](#)

[Accessories](#)

[Cable Lugs](#)

[Clips](#)

[Connectors](#)

[Grounding Cables](#)

[Instrumentation Cables](#)

[Kits](#)

[Test Leads](#)

[Temporary Protective Grounds](#)

[Wire & Cable](#)

Industry Solutions

[Aerospace](#)

[Battery](#)

[Instrumentation](#)

[Medical](#)

[Military & Defense](#)

[Paint Grounding](#)

[Substation Maintenance](#)

[Test and Measurement](#)

[Underground Sensing](#)

Quick Links

[About Us](#)

[Full Catalog](#)

[Free Guides](#)

[FAQs](#)

[Media & Downloads](#)

[Blog](#)

[Contact Us](#)

[Policies](#)



Mueller Electric USA

2850 Gilchrist Rd. Building 5A, Akron, OH 44305

sales@muellerelectric.com

Toll Free: 1(800) 955 - 2629

Phone: (330) 780 - 2525

Fax: 330-780-2524

Mueller Electric Europe

Unit 9, Castle Park Industrial Estate, Queens Drive,
Nottingham NG2 1AH, United Kingdom

EUsales@muellerelectric.com

Tel: +44 (0) 1159 933300

Fax: +44 (0) 1159 933301

Mueller Electric China

7th Floor, Bldg-3, No.1295 Xin Jinqiao Rd, Shanghai, China

P.C.:201206

TEL: +86 185 1626 6177



MIL-STD RoHS IEC 1010 COMPLIANT **SP** DSCC **C E** **UL**

© Copyright 2023 Mueller Electric. All Rights Reserved.

Experience: ia

Site crafted by **Robintek: Columbus Website Design**