

Hand Held - Plastic Enclosures (Clipper Series)

[Home](#)
[Products](#)
[Distributors](#)
[Technical](#)
[Contact Us](#)
[Other Options](#)

Path: [Home](#) > [Enclosure Index](#) > **Plastic - Hand Held (Clipper Series)**



(click to enlarge)

**Assembled View
(Top)**



(click to enlarge)


**Assembled View
(Bottom)**













(click to enlarge)

Open View

Key Features:

- The Clipper series is a British designed hand held enclosure (originally sold under the West Hyde Enclosures Ltd. name).
- Ideally suited for mounting small printed circuit boards for use in hand held applications.
- Ergonomically styled for a secure and comfortable grip.
- Molded in a choice of black (RAL 9005) or grey (RAL 9018) - flame retardant ABS plastic.
- Satin texture finish.
- Complete with top & bottom, removable front panel, battery door (except on the smallest size) and three self tapping screws.
- The top panel has a flat display area, perfect for labels, silk screening, membrane keypads or easily machined.
- The base is molded with bosses for easy P.C. board mounting.
- The removable end panel is securely clamped by the two box halves and easily customized or replaced by an infra-red panel.
- Battery compartment (except on the smallest size) suitable for either a 9V (PP3) or 2 x AA batteries.
- Battery compartment has an easily removable cover which also covers one of the three assembly screws.
- Screws are color matched to enclosure (nickel plated screws with grey enclosures and black plated with black enclosures).
- P.C. board standoffs molded into interior (see drawings for locations).
- Lap joint construction provides protection against access of dust and splashing water.
-  Link here to [photo tables](#) of each part number (shown in black).

Part Number	Color	Battery Door	Reader File	 Drawing File Size	AutoCAD .dwg File (zipped)	.zip File Size	Units	Length	Width	Enclosure Depth (With Lid)
001100 001111	Black Grey	No		131K		160K	Inches	1.57	2.36	0.73
							mm	40	60	18.5
001102 001113	Black Grey	Yes		215K		177K	Inches	3.35	2.36	0.87
							mm	85	60	22
001104 001115	Black Grey	Yes		134K		176K	Inches	4.13	2.36	0.87
							mm	105	60	22
001106 001117	Black Grey	Yes		129K		181K	Inches	4.92	2.76	0.87
							mm	125	70	22

 Link here to [photo tables](#) of each part number (shown in black)

- NOTE:**
- For a broader selection of this type of plastic handheld enclosure link to our [1593 series](#).

Color Options:



(click to enlarge)


Black (RAL 9005)




(click to enlarge)

Grey (RAL 9018)

Accessories



(click to enlarge)



(click to enlarge)

Pocket / Belt Clip

Part Number	Description
001150	Infrared Translucent - Replacement End Panel
001151	Pocket/Belt Clip (Black)
001152	Pocket/Belt Clip (Grey)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 2006 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>