

# 12W EU Wall Plug Adapter

**multicomp** PRO



## Features

- Euro Plug Top
- DOE Level VI Efficiency
- Overcurrent Protection
- Short Circuit Protection
- 1 Year Warranty
- EN62368 Approved
- DC Cable Length: 1500mm


**RoHS  
Compliant**

Models		MP009259	MP010792	MP010793	MP010794
Output	DC Voltage	5V DC	9V DC	12V DC	24V DC
	Rated Current	2 amp	1.33 amp	1 amp	0.50 amp
	Current Range	0-2 amp	0-1.33 amp	0-1 amp	0-0.5 amp
	Rated Power	12Watt			
	Ripple & Noise	200mVp-p max			
	Output Regulation	±5%			
	Output Connector	2.1mm x 5.5mm x 12mm C+ve			
Input	Voltage Range	90-264V AC			
	Frequency Range	47-63Hz			
	Input Current	1.2amp Max			
	Inrush Current	40amp Max			
	Standby Power	0.1W Max			
	Leakage Current	0.25amp Max			
	Input Connector	UK			
Environment	Operating Temp	0°C to 40°C			
	Cooling	Convection			
	Temperature Coefficient	0.05%/°C			
	Humidity	5~95%RH(non-condensing)			
	Storage Temp	-20°C to +80°C			
Safety & EMC	Safety Standards	CE EN62368-1			
	EMC Emissions	EN55032,EN55035, EN61000-3-2 2014, EN61000-3-3 2013			

# 12W EU Wall Plug Adapter

**multicomp** PRO

## Mechanical Specification



Dimensions : Millimetres

## Part Number Table

Description	Part Number
Wall Plug Adapter, 12W, 5V DC, 2A, EU Plug	MP009259
Wall Plug Adapter, 12W, 9V DC, 1.33A, EU Plug	MP010792
Wall Plug Adapter, 12W, 12V DC, 1A, EU Plug	MP010793
Wall Plug Adapter, 12W, 24V DC, 0.5A, EU Plug	MP010794

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp** PRO