

Wall bracket - OCS MOUNT 1210 SET



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Mounting plate, set of 2 pieces incl. screws for housing size of 12" x 10", material: polycarbonate, color: light gray



Your advantages

- Internationally certified housing system
- Special plastic ensures safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial Data

Item number	1471782
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	A13
Product Key	ACFDBZ
GTIN	4063151881320
Weight per Piece (including packing)	177.418 g
Weight per Piece (excluding packing)	177.418 g
Customs tariff number	39269097
Country of origin	EE

Wall bracket - OCS MOUNT 1210 SET



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Technical Data

Notes

Assembly instruction:	Only use the screws supplied for mounting.
Assembly instruction:	Secure the mounting feet or flanges using the screws provided. If mounting the housing on a wall, select the appropriate screw type for the wall construction.

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing series	OCS

Dimensions

Width	65 mm
Height	255 mm
Depth	8 mm

Material specifications

Flammability rating according to UL 94	V2
Insulating material	PC
Surface characteristics	untreated
Housing material	Polycarbonate

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	Mast mounting or wall mounting
---------------	--------------------------------

Wall bracket - OCS MOUNT 1210 SET



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Classifications

ECLASS

ECLASS-11.0	27182702
-------------	----------

Wall bracket - OCS MOUNT 1210 SET

1471782

<https://www.phoenixcontact.com/us/products/1471782>



Accessories

Screwdriver

Screwdriver - SZK PH2 VDE - 1205163

<https://www.phoenixcontact.com/us/products/1205163>



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

Tool set

Tool set - SF-BIT SET - 1212545

<https://www.phoenixcontact.com/us/products/1212545>



Bit set, with SF-UBH universal bit holder, with 25 mm long bladed/crosshead bits (PZ and PH), 10-part, in compact plastic box

Wall bracket - OCS MOUNT 1210 SET

1471782

<https://www.phoenixcontact.com/us/products/1471782>



Screwdriver

Screwdriver - SF-PH 2-100 - 1212560

<https://www.phoenixcontact.com/us/products/1212560>



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com