


ACCESSORIES AND FLOW RANGES

FP-5000 Series Paddlewheel Sensors

FP-5300, shown smaller than actual size. See page F-27 for details. Or visit omega.com fp5100_fp5300



Accessories for FP-5100, FP-5300 and FP8500

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)	
Model No.	Description
FMK-515-3P3	Paddlewheel sensor only for wet-tap (½ to 4")
FMK-515-3P4	Paddlewheel sensor only for wet-tap (5 to 8")
FMK-515-3P5	Paddlewheel sensor only for wet-tap-double extended housing (10 to 36")
FMK-1538-2	Replacement rotor–PVDF (standard black color)
FMK-1538-4	Replacement rotor–ETFE
FMK-1546-1	Titanium rotor pin (standard)
FMK-1546-2	Hastelloy C rotor pin
FMK-1546-3	Tantalum rotor pin
FMK-1546-4	Stainless steel rotor pin
FPP-1220-0021	Sensor housing O-rings–FKM (standard)
FPP-1224-0021	EPR O-ring
FPP-1228-0021	Perfluoroelastomer O-ring
PH-31542-TC	Sensor cap (red)
FMK-31934	Conduit cap
FMK-51545	Ceramic rotor pin
FMK-51545-1	PVDF rotor pin and replacement rotor (natural color)
FMK-51546	Sleeved rotor
PHA-86	1¼" Pipe adaptor (PVDF, for In-line sensors)

Accessories for the FP-5600 and FP8500A Series

Model No.	Description
FMK-2536-3P3	Low flow paddlewheel sensor only for wet-tap (½ - 4")
FMK-2536-5	PVDF (natural) replacement rotor and pin
FMK-1546-1	Titanium rotor pin
FMK-1546-2	Hastelloy-C rotor pin
FMK-1546-3	Tantalum rotor pin
FMK-1546-4	Ceramic rotor pin
FPP-1220-0021	FPM-FKM O-Ring
FPP-1224-0021	EPDM O-Ring
FPP-1228-0021	FFKM-Perfluoroelastomer O-Ring
FMK-31536-1	Polypro plug (standard)
FMK-31934	Conduit cap
FPM-5000-SCAK	Conduit adaptor kit

Ranges (in gallons per minute) for FP8500, FP-5300, FP-5200, FP-5100

Pipe Size (in)	FP-5300 Min. Flow	FP-5200 Min. Flow	FP-5600 FP8500A Min. Flow	Max Flow
0.5	1	1.6	0.3	19
0.75	1.7	2.7	0.5	34
1	2.7	4.4	0.8	54
1.25	4.7	7.4	1.4	94
1.5	6.4	10.1	1.9	127
2	10.6	16.8	3.2	210
2.5	15	24	4.5	300
3	24	37	7.0	461
4	40	63	12	794
5	63	100	19	1247
6	91	144	27	1801
8	156	250	47	3119
10	246	393	74	4915
12	349	559	105	6977

Metal Flow Sensor Accessories for FP-5200

Model No.	Description
FP-52509	Rotor assembly (with bearings)
FP-52618	Gasket
FP-52628	Cap kit (gasket and hardware)



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters