

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200795044](#)  
**Status:** **Active**  
**Overview:** Brad Ultra-Lock Connection System  
**Description:** Ultra-Lock (M12) Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 22 AWG, Black PVC Cable, 5.0m (16.40') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Industrial Cordsets  
 Series [120079](#)  
 Connector End A Ultra-Lock (M12)  
 Connector End B Pigtail  
 IP Rating IP69K  
 Material - Contact Bronze  
 Overview [Brad Ultra-Lock Connection System](#)  
 Product Name Ultra-Lock (M12)  
 Region Europe  
 Taxonomy Circular Industrial Cordsets  
 Type Single Ended  
 UPC 883906777036

**Physical**

Cable Diameter 5.80mm (.230")  
 Cable Length 5.0m (16.40')  
 Color - Cable Jacket Black  
 Coupling Style Push to Lock  
 Gender Female-Pigtail  
 Keyway A-coded  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body TPU  
 Material - Coupling Nut Stainless Steel  
 Material - O-Ring FPM  
 Material - Plating Mating Gold  
 Net Weight 99.000/g  
 Orientation 90° to Pigtail  
 Poles 5  
 Temperature Range - Operating -25° to +85°C  
 Wire Size AWG 22  
 Wire/Cable Type UL 2464

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 60V

**Material Info**

Engineering Number W05001E03M050

**Reference - Drawing Numbers**

Sales Drawing 1200790281-000



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

Not Relevant

Not Reviewed

Not Contained

CER\_4000410038\_00\_000.pdf

CER\_4000410299\_00\_000.pdf

**Search Parts in this Series**

[120079 Series](#)

This document was generated on 11/18/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**