

Specification Sheet

Part Number: 151-04031



No drilling or extra hardware required – just secure to steel surface. Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse, 360-degree rotation and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.

Magnetic Clip, Large, 1", Neodymium Magnet/POM/ST, 15lb Pull Force, Black, 10/Bag

Article Number 151-04031

Type MAGC15L

Color Black (BK)

Quantity Per bag

Product Description

Magnetic clips are designed to route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle by pushing it into the clip and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The clips are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description	Magnetic Clip, Large, 1", Neodymium Magnet/POM/ST, 15lb Pull Force, Black, 10/Bag
Global Part Name	MAGC15L-NDFEB35/POM/ST-BK
Length L (Imperial)	1.24
Length L (Metric)	31.5
Fixation Method	Magnet
Height H (Imperial)	1.24
Height H (Metric)	31.5
Depth D (Imperial)	0.23
Depth D (Metric)	5.7
Diameter D (Imperial)	0.91
Diameter D (Metric)	23.2
Material	Neodymium alloy 35M (NDFEB35) Polyacetal (POM) Steel (ST)
Material Shortcut	POM NDFEB35 ST
Halogen Free	Yes

Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	8505110070

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)