

## Specification Sheet

Part Number: 170-01164

Self-wrapping woven sleeving made of fiberglass and PET polyester protects against chewing damage.

Provides good protection against abrasion, UV and weathering, vibration and impact.

Quick and easy installation and removal, ideal for retrofitting.

Lightweight material won't add significant weight to the installation.

Resists acids, solvents and micro-organisms for extended performance in industrial environments.



Braided Sleeving, Twist-In Rodent-Repellent Wrap, 32mm Dia. FG/PET, White, 49.2 ft/l

Article Number 170-01164

Type Twist-In-RR-32

Color White (WH) Black (BK)

Quantity Per reel

Product Description Twist-In Rodent-Repellent Wrap is a self-closing fiberglass sleeving used to bundle cables and hoses and protect against rodents in infestation-prone areas such as automotive, railways, telecom, underground and waste treatment systems.

Short Description Braided Sleeving, Twist-In Rodent-Repellent Wrap, 32mm Dia. FG/PET, White, 49.2 ft/l

Global Part Name	Twist-In-RR-32-PET/GF-BK/WH
Bundle Diameter Min (Imperial)	1.14
Bundle Diameter Min (Metric)	29
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.8
Wall Thickness WT (Metric)	0.8
Material	Glass Fiber (GF) Polyester (PET)
Material Shortcut	GF PET
Flammability	FMVSS 302
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Certification/Specification	EN [45545-2]
Package Quantity (Imperial)	49.2
Package Quantity (Metric)	15
Customs Number	5808100000
Reel Weight (Imperial)	2.62
Reel Weight (Metric)	1.19

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)