

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0347928081**
Status: **Active**
Overview: Mini50 Connection Systems
Description: Mini50 Unsealed Vertical Header, Single Row, 8 Circuit, Polarization Option B, Gray, Tape and Reel

Documents:

3D Model	Application Specification AS-34791-020-CH-001 (PDF)
Drawing (PDF)	Test Summary 347910020-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34791-020-001 (PDF)	

General

Product Family	PCB Headers
Series	34792
Application	Automotive, Power, Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini50 Connection Systems
Product Name	Mini50
Taxonomy	PCB Headers and Receptacles
UPC	889056918923

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	1.541/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001
---------------------------	---------------------------------------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[34792 Series](#)

Mates With

[34791 Mini50 Unsealed Single Row Receptacle](#)

Product Specification
Sales Drawing
Test Summary

PS-34791-020-001
SD-34792-001-001
347910020-TS-000

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION