CC-E-VA-6.6



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Test Blocks + Current Sockets

General Information

Extended Product Type: CC-E-VA-6.6

Product ID: 1SNA166625R2000 EAN: 3472591666250

Catalog Description: CC-E-VA-6.6 Current Sockets

Long Description: Short-circuited type contacts for measurement, calibration and distribution

applications. Make before break principle: — The circuit is automatically s horted with the insertion of the plug. — The circuit closes automatically when the plug is removed. — This system guarantees a complete safety. —

By convention, green coding is for current circuit.

Ordering

Color: Green

Minimum Order Quantity: 1 piece

Customs Tariff Number: 85361010

Popular Downloads

Data Sheet, Technical Information: 1SND169023D0202

Instructions and Manuals: 1SND169023D0202

Dimensions

Product Net Width: 50 mm

Product Net Height: 74 mm

Product Net Depth / Length: 57 mm

Product Net Weight: 150 g

Technical

Connection Type: Ring - Tongue

Function: Current transformers application

Connecting Capacity Main Circuit: Stud / Flexible 1x 0.34 ... 10 mm²

Rated Current (I_n): Main Circuit 15 A

Rated Short-time Withstand

Current (Icw):

for 1 s 200 A

Rated Voltage (U_r): 400 V

Rated Impulse Withstand Voltage 4000 V

 (U_{imp}) :

Pollution Degree: 3

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Insulation Material: Polycarbonate

Environmental

Ambient Air Temperature: Operation -10 ... +55 °C

Storage -25 ... +70 °C

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225003U1001

EAC Certificate: 1SND160001A1100

Environmental Information: 1SND220073E1000

Instructions and Manuals: 1SND169023D0202

Classifications

Object Classification Code: X

ETIM 4: EC000902 - (Knife) disconnect terminal block

ETIM 5: EC000902 - (Knife) disconnect terminal block

ETIM 6: EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units: 1 piece

Package Level 1 Width: 74 mm

Package Level 1 Depth / Length: 86 mm

Package Level 1 Height: 51 mm

Package Level 1 Gross Weight: 0.15 kg

Package Level 1 EAN: 3472591666250

Package Level 2 Units: 35 piece

Package Level 3 Units: 1680 piece

Product Packing Type: Box

