



Quality Products. Service Excellence.

Aluminum Rack Panels *PBPA Series*

Features:




- Constructed of 8-gauge (0.125") 5052-H32 Aluminum.
- Fits standard EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder paint or unfinished.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Note: We are reducing our offering to focus on 1U up to 10U. Larger sizes are available by special order. Minimums apply.

Accessories


- Mounting Hardware
- Rack Rail Reducer Panel



We are making changes to the design of this product.

We are enclosing the rack mounting holes and rounding all edges.

Old Design (Left) | New Design (Right)



Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height	Qty of	
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Part No.	Rack	Panel	
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matte White	Unfinished	Units	Height	
							Points	
PBPA19001BK2	PBPA19001BK	PBPA19001GY2	PBPA19001LG2	PBPA19001WH	PBPA19001UNF	1U	1.75	4
PBPA19003BK2	PBPA19003BK	PBPA19003GY2	PBPA19003LG2	PBPA19003WH	PBPA19003UNF	2U	3.50	4

Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height		Qty of
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Part No.	Rack	Panel	Mounting
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matte White	Unfinished	Units	Height	Points
PBPA19005BK2	PBPA19005BK	PBPA19005GY2	PBPA19005LG2	PBPA19005WH	PBPA19005UNF	3U	5.25	4
PBPA19007BK2	PBPA19007BK	PBPA19007GY2	PBPA19007LG2	PBPA19007WH	PBPA19007UNF	4U	7.00	4
PBPA19008BK2	PBPA19008BK	PBPA19008GY2	PBPA19008LG2	PBPA19008WH	PBPA19008UNF	5U	8.75	4
PBPA19010BK2	PBPA19010BK	PBPA19010GY2	PBPA19010LG2	PBPA19010WH	PBPA19010UNF	6U	10.50	8
PBPA19012BK2	PBPA19012BK	PBPA19012GY2	PBPA19012LG2	PBPA19012WH	PBPA19012UNF	7U	12.25	8
PBPA19014BK2	PBPA19014BK	PBPA19014GY2	PBPA19014LG2	PBPA19014WH	PBPA19014UNF	8U	14.00	8
PBPA19015BK2	PBPA19015BK	PBPA19015GY2	PBPA19015LG2	PBPA19015WH	PBPA19015UNF	9U	15.75	8
PBPA19017BK2	PBPA19017BK	PBPA19017GY2	PBPA19017LG2	PBPA19017WH	PBPA19017UNF	10U	17.50	8

Clearance (Available while supplies last)

Part No.	RAL9005	Part No.	ANSI61	Part No.	RAL7035	Unfinished		
RAL9005	Remaining	ANSI61	Remaining	RAL7035	Remaining	Part No.	Remaining	Rack
Semi-Gloss Black	Stock	Dark Gray	Stock	Light Gray	Stock	Unfinished	Stock	Units
PBPA19019BK2	0	PBPA19019GY2	0	PBPA19019LG2	1	PBPA19019UNF	5	11U
PBPA19021BK2	0	PBPA19021GY2	2	PBPA19021LG2	0	PBPA19021UNF	12	12U
PBPA19022BK2	0	PBPA19022GY2	9	PBPA19022LG2	0	PBPA19022UNF	4	13U
PBPA19024BK2	0	PBPA19024GY2	2	PBPA19024LG2	0	PBPA19024UNF	4	14U
PBPA19026BK2	6	PBPA19026GY2	7	PBPA19026LG2	6	PBPA19026UNF	0	15U
PBPA19028BK2	2	PBPA19028GY2	1	PBPA19028LG2	1	PBPA19028UNF	7	16U
PBPA19029BK2	1	PBPA19029GY2	10	PBPA19029LG2	8	PBPA19029UNF	19	17U
PBPA19031BK2	1	PBPA19031GY2	2	PBPA19031LG2	1	PBPA19031UNF	0	18U

Stock levels were last updated on September 12, 2023

Data subject to change without notice

© 2023. Hammond Manufacturing Ltd. All rights reserved.