

Product information

00 21 06 HK S

Tool Case "BIG Basic Move" Plumbing



- Equipped with four KNIPEX tools, a total of 31 brand tools, partly VDE-tested according to DIN EN 60900
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Two metal flip locks and a three-digit combination lock for secure locking of the cover
- Label field with two stickers for individual labelling
- Max. payload: 20 kg
- Volume: 33 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 31 tool pockets
- First tool board with ten tool pockets and an elastic strap on the cover side and eleven narrow and one large tool pocket on the base side
- Second tool board with ten tool pockets and an elastic strap on the base side and a document compartment on the cover side
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 13 large tool pockets and a flat compartment
- With a total of 54 inserting options







General

Article No.	00 21 06 HK S
EAN	4003773084266
Weight	10,855 g
Dimensions	264 x 436 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	430 mm (350 mm)
Dimension exterior (interior) height mm	280 mm (200 mm)
Dimension exterior (interior) depth mm	515 mm (480 mm)

Content

70 06 160	1 x Diagonal Cutter ⚠ 1000V 
86 03 250	1 x Pliers Wrench pliers and a wrench in a single tool 
88 01 250	1 x KNIPEX Alligator® Water Pump Pliers 
88 01 300	1 x KNIPEX Alligator® Water Pump Pliers 
306125	1 x Haunstetter PUK® Junior Hacksaw (150 x 240 mm)
1664000000	1 x Heyco Cutter (18 mm)
90958	1 x Heyco Express key (M 10)
L240 00055	1 x Knipex Folding ruler Stabila series 400 (200 mm)
75040-015	1 x Picard Flat brush (40 mm)

Content	
75060-005	1 x Picard steel wire brush, 5-row (280 mm)
75063-000	1 x Picard Plaster bowl (127 x 94)
75075-040	1 x Picard Painter's spatula 40 mm, wood, high quality (40 mm)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
3003010119	1 x Ruthe Locksmith's hammer, 300 g (300 g)
15212	1 x Stabila Carpenter's pencil
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)
031582	1 x Wera Screwdrivers for slotted screws 1160i (0,6 x 3,5 x 100 mm)
031587	1 x Wera Screwdrivers for slotted screws 1160i (1,0 x 5,5 x 125 mm)
031588	1 x Wera Screwdrivers for slotted screws 1160i (1,2 x 6,5 x 150 mm)
031601	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH1 x 80 mm)
031603	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH2 x 100 mm)
6135-0	1 x Zenten Pipe cutter (3 - 35 mm / 1/8 - 1 1/2")
Accessories	
00 21 06 LE	Tool Case "BIG Basic Move" empty,

technical change and errors excepted

