

**52 Pc. iTorque Bit Set - 7-26 In/lbs.**

Item No.	Description	Case Pack
28892	iTorque Bit Set	1
<b>Slotted:</b> 4.5, 5.5, 6.5, 8.0mm <b>Phillips:</b> #0, 1, 2, 3		
<b>TORX:</b> T6, T7, T8, T9, T10, T15, T20, T25, T27, T30		
<b>Pozidriv:</b> #0, 1, 2, 3 <b>Square:</b> #1, 2, 3		
<b>Hex In:</b> 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"		
<b>Hex Metric:</b> 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm		
<b>Torq Set:</b> #4, 5, 6, 8 <b>Tri-wing:</b> #0, 1, 2, 3, 4		
iTorque Handle 7-26 In/lbs. & 1/4" Bit Holder Adapter		

**52 Pc. iTorque Bit Set - 9-50 In/lbs.**

Item No.	Description	Case Pack
28896	iTorque Bit Set	1
<b>Slotted:</b> 4.5, 5.5, 6.5, 8.0mm <b>Phillips:</b> #0, 1, 2, 3		
<b>TORX:</b> T6, T7, T8, T9, T10, T15, T20, T25, T27, T30		
<b>Pozidriv:</b> #0, 1, 2, 3 <b>Square:</b> #1, 2, 3		
<b>Hex In:</b> 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"		
<b>Hex Metric:</b> 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm		
<b>Torq Set:</b> #4, 5, 6, 8 <b>Tri-wing:</b> #0, 1, 2, 3, 4		
iTorque Handle 9-45 In/lbs. & 1/4" Bit Holder Adapter		

**24 Pc. ESD Safe TorqueVario-S Micro Bit Set**

Item No.	Description	Case Pack
28895	Torque Micro Bit Set	1
<b>Slotted:</b> .8, 1.2, 1.5, 1.8, 2.0mm		
<b>Phillips:</b> #000, 00, 0 & <b>Hex:</b> .7, .9, 1.3mm		
<b>TORX:</b> T1, T2, T3, T4, T5, T6		
<b>Pentelobe:</b> PL1, PL2, PL3, PL4		
Adjustable Torque Handle: .04-.46 Nm (+/- 10%)		

**Torque QuickCheck**

Item No.	Description	Case Pack
28897	Torque Quick Checker	1
Torque Checker, Adapter blades & 2 batteries		

**T-Handle TorqueControl TORX® Blade**

Item No.	Description	Case Pack
28903	T15 x 130mm	3
28904	T20 x 130mm	3
28905	T25 x 130mm	3
28906	T27 x 130mm	3
28907	T30 x 130mm	3
28908	T40 x 130mm	3

**T-Handle TorqueControl TORXPlus® Blade**

Item No.	Description	Case Pack
28910	IP15 x 130mm	3
28911	IP20 x 130mm	3
28912	IP25 x 130mm	3
28913	IP27 x 130mm	3
28914	IP30 x 130mm	3

**T-Handle TorqueControl Hex Metric Blade**

Item No.	Description	Case Pack
28916	3.0 x 130mm	3
28917	4.0 x 130mm	3
28918	5.0 x 130mm	3
28919	6.0 x 130mm	3

**TorqueFix Quick Release Bit Holder**

Item No.	Description	Case Pack
28925	1/4" x 125mm	3

**TorqueFix Adapter For 1/4" & 3/8" Sockets**

Item No.	Description	Case Pack
28926	1/4" x 100mm	3

**TorqueFix T-Handle**

Item No.	Description	Case Pack
28931	53.1 In/lbs.-6 Nm	1
28933	70.8 In/lbs.-8 Nm	1
28935	88.5 In/lbs.-10 Nm	1
28937	106.2 In/lbs.-12 Nm	1
28938	110.6 In/lbs.-12.5 Nm	1
28939	123.9 In/lbs.-14 Nm	1

**Adjustable TorqueVario STplus T-Handle**

Item No.	Description	Case Pack
28940	44.3 - 123.9 In/lbs. 5 - 14 Nm (Scale is shown in Nm only)	1

**easyTorque Screwdriver Handles**

Item No.	Description	Case Pack
29205	4.4 In/lbs. - 0.5 Nm	3
29206	5.3 In/lbs. - 0.6 Nm	3
29209	7.9 In/lbs. - 0.9 Nm	3
29211	9.7 In/lbs. - 1.1 Nm	3
29212	10.6 In/lbs. - 1.2 Nm	3
29214	12.4 In/lbs. - 1.4 Nm	3
29220	17.7 In/lbs. - 2.0 Nm	3
29225	22.1 In/lbs. - 2.5 Nm	3
29230	26.6 In/lbs. - 3.0 Nm	3
29238	33.6 In/lbs. - 3.8 Nm	3
29241	35.4 In/lbs. - 4.0 Nm	3
29245	39.8 In/lbs. - 4.5 Nm	3
29251	44.2 In/lbs. - 5.0 Nm	3

**easyTorque TORX Screwdrivers**

Item No.	Description	Case Pack
29232	T5 - 4.4 In/lbs.-0.5Nm	3
29233	T6 - 5.3 In/lbs.-0.6Nm	3
29234	T7 - 8.0 In/lbs.-0.9Nm	3
29236	T8 - 10.6 In/lbs.-1.2Nm	3
29237	T9 - 12.4 In/lbs.-1.4Nm	3
29239	T10 - 17.7 In/lbs.-2.0Nm	3
29242	T15 - 26.6 In/lbs.-3.0Nm	3
29243	T20 - 35.4 In/lbs.-4.0Nm	3
29244	T25 - 44.2 In/lbs.-5.0Nm	3

**easyTorque TORXPlus Screwdrivers**

Item No.	Description	Case Pack
29246	IP5 - 4.4 In/lbs.-0.5Nm	3
29247	IP6 - 5.3 In/lbs.-0.6Nm	3
29248	IP7 - 8.0 In/lbs.-0.9Nm	3
29249	IP8 - 10.6 In/lbs.-1.2Nm	3
29252	IP9 - 12.4 In/lbs.-1.4Nm	3
29253	IP10 - 17.7 In/lbs.-2.0Nm	3
29254	IP15 - 26.6 In/lbs.-3.0Nm	3
29255	IP20 - 35.4 In/lbs.-4.0Nm	3
29256	IP25 - 44.2 In/lbs.-5.0Nm	3