

20-Bit Electric Precision Screwdriver Set - Portable/Mini Battery Powered Bit Driver Kit for Electronics, Laptop, Computer, Tablet & Phone Repairs - Magnetic - Cordless

Product ID: CTK20PCEDRIVE



This cord-less screwdriver is the ideal tool to dismantle and reassemble electronic devices during repairs. The battery powered driver set includes a precision electric screwdriver (2 x AAA batteries included), 20 micro bits, and a magnetizer/demagnetizer, housed in a durable soft carrying case. The bits included have been specially selected for compatibility with most major brands of smartphones, tablets and laptops including but not limited to Apple iPhones, iPads, Macbooks, Samsung Galaxy, HP and Acer Chromebooks, Lenovo ThinkPads.

The premium electric driver included with this kit has several features designed for hassle-free repairs.

- A built-in LED work light illuminates the area that the driver is operating in, ensuring you can clearly see shadowless details, regardless of the lighting in your repair area.
- Battery operated forward and reverse modes with 0.25 to 0.35 N.m of torque, ensures you can effortlessly install and remove screws without the wrist strain that comes with manual drivers.
- The included magnetizer/demagnetizer gives you the option to magnetize the driver to ensure screws are easy to install/remove without losing them. Plus, the head can be demagnetized for IT repairs on devices that may be sensitive to magnets.
- Quick changing batteries ensure uninterrupted operation.

This kit features 20x4mm bits specially selected for extensive compatibility with major brands of smartphones, tablets and laptop computers. Bits Included:

- Philips (crosshead): PH000, PH00, PH0, PH1
- Slot (flathead): SL1.0, SL1.5, SL2.0
- Torx: T5
- Torx Security: T6, T8

- Hexagonal: H2.5, H3.0
- Pentalobe: P20.8, P51.2, P61.5
- Spanner: U3.0
- Tri Wing: Y0.6, Y2.5
- Triangle: 3.0
- Robertson: S0

Included with the electric driver is a durable soft carrying case.

CTK20PCEDRIVE is backed by a StarTech.com 2-year warranty with free 24/5 multi-lingual North American based technical support. StarTech.com has been the IT professionals' choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Dismantle and reassemble electronic devices during repairs

Features

- **PRECISION BATTERY-POWERED DRIVER:** This portable electric precision screwdriver is the perfect tool to dismantle & assemble electronics/devices; The cordless aluminum driver is battery powered (2xAAA incl.); LED light, buttons for forward and reverse modes
- **PRECISION BITS:** 20 piece set; Philips (PH000/PH00/PH0/PH1), Slot (SL1.0/SL1.5/SL2.0), (TORX T5), TORX Security T6/T8, HEXAGON (H2.5/H3.0), Pentalobe P2(0.8)/P5(1.2)/P6(1.5), Spanner (U3.0), Tri Wing (Y0.6/Y2.5), Triangle 3.0, Robertson S0
- **WORKS WITH MAJOR DEVICES:** The bits included have been specially selected for compatibility with major brands of smartphones, tablets and laptop computers incl. but not limited to iPhone/iPad/Samsung Galaxy/Dell/HP/Acer/Lenovo ThinkPad/Macbook/Chromebook
- **HASSLE-FREE OPERATION:** Mini power operated driver w/0.35 N.m of torque (max) & 110 rpm (max) helps to prevent screw damage; Quick change batteries ensure uninterrupted operation & magnetizer/demagnetizer makes this kit ideal for IT/repair shops
- **STARTECH.COM ADVANTAGE:** The compact/small electric precision screwdriver supports standard 4mm micro bits making it easy to add/replace bits; It's backed for 2-years by StarTech.com, incl. free lifetime 24/5 North America based multi-lingual tech support

Performance

Warranty	2 Years
General Specifications	Power Supply: 2x AAA Batteries (included)
	Speed: 110 RPM
	Output Torque: 0.25 - 0.35 N.m
	Supported Bit Size: 4mm
	Included Bit Size: H4x28mm
	Included Bits: Philips (crosshead) PH000, PH00, PH0, PH1
	Slot (flathead) SL1.0, SL1.5, SL2.0
	Torx T5
	Torx Security T6, T8
	Hexagonal H2.5, H3.0
	Pentalobe P20.8, P51.2, P61.5
	Spanner U3.0
	Tri Wing Y0.6, Y2.5
	Triangle 3.0
	Robertson S0

Physical Characteristics

Color	Silver
Materials	Aluminum
Product Length	7.1 in [18.0 cm]
Product Width	0.6 in [1.6 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	1.8 oz [52.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	2.8 in [7.0 cm]
Package Width	9.1 in [23.0 cm]
Package Height	16.9 in [43.0 cm]
Shipping (Package) Weight	8.8 oz [250.0 g]

What's in the Box

Included in Package	1 - Precision Screwdriver
	1 - 20 Piece Bit Set
	1 - Demagnetizer
	1 - Quick-Start Guide
	2 - AAA Battery

****Product appearance and specifications are subject to change without notice.***