

## 1.5m High Speed HDMI Cable – Ultra HD 4k x 2k HDMI Cable – HDMI to HDMI M/M

**Product ID:** HDMM150CM



The HDMM150CM 1.5m High Speed HDMI cable comes in a non-standard 5 foot cable length allowing for a convenient connection distance and enabling you to position your HDMI-enabled devices as needed.

The cable features two gold-plated HDMI male connectors to provide a dependable HDMI to HDMI connection, while the unique cable length makes it perfect for watching videos from your laptop on your HDMI TV or for boardroom presentations when connecting your laptop to an HDMI-enabled projector.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM150CM 5ft HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

### Certifications, Reports and Compatibility



### Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles,

projectors etc.

## Features

- 2x HDMI male connectors
- Offers 5' in cable length
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

---

### Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

---

### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	60% at 25C

---

### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG

Cable Length	4.9 ft [1.5 m]
Product Length	4.9 ft [1.5 m]
Product Width	0.8 in [21.0 mm]
Product Height	0.5 in [1.2 cm]
Weight of Product	3.8 oz [107.9 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.5 in [12.0 mm]
Shipping (Package) Weight	3.8 oz [107.9 g]

---

**What's in the Box**

Included in Package	1 - 1.5m High Speed HDMI Cable - HDMI - M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***