

USB-C to USB-C Cable - M/M - 1 m (3 ft.) - USB 3.0 (5Gbps)

Product ID: USB315CC1M



This USB 3.2 Gen 1 USB-C to USB-C cable lets you connect a USB 3.2 Gen 1, USB Type-C device, such as a hard drive or mobile device, to the USB-C port on your computer, or charger. The cable is also compatible with Thunderbolt 3 ports.

Connect your newer USB-C mobile devices, such as the Samsung Galaxy S8, S8+, Nexus 6P, and 5X phones, to your computer. The cable delivers up to a 3 amp (60W) charge, and supports data transfer speeds of up to 5Gbps.

With up to 3A of power output, you can also use the USB Type-C cable to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect your laptop to your USB-C wall charger.

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

You'll also be able to connect your USB 3.2 Gen 1 peripheral devices, such as hard drive enclosures and docks, to your laptop.

The USB315CC1M from StarTech.com comes with a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 device such as a portable hard drive or docking station to a USB-C laptop or desktop computer

- Charge and sync your USB-C mobile digital devices with your computer
- Charge your USB-C devices with a wall charger, car charger or power bank
- Power your USB-C enabled laptops with a USB Type-C wall charger

Features

- Supports data transfer rates up to 5Gbps (USB 3.2 Gen 1)
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Analog Resolutions	4K @ 60Hz
Type and Rate	USB 3.0 - 5 Gbit/s

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)

Power

Power Delivery	60W
----------------	-----

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical

Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/32 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.4 mm]
Weight of Product	1.4 oz [39.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.7 oz [47.0 g]

What's in the Box

Included in Package	1 - USB-C cable
---------------------	-----------------

**Product appearance and specifications are subject to change without notice.*