


3 foot (1m) Durable White USB-C to Lightning Cable - Heavy Duty Rugged Aramid Fiber USB Type A to Lightning Charger/Sync Power Cord - Apple MFi Certified iPad/iPhone 12

Product ID: RUSBCLTMM1MW



This 1 m (3 ft.) white USB C to Lightning cable withstands the daily demands of charging and syncing your iPad, iPhone or other mobile devices featuring the Lightning connector. Tested to endure strenuous wear and tear and winter and summer in-car use, the strong and rugged cable is a must-have for both business and consumer applications.

The durable USB C to Lightning cable has aramid fiber reinforcement that shelters it from the stress of frequent bends and twists. This also lets the heavy duty cable flex without over-stretching and strengthens the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable and environmentally friendly

The reinforced cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle. Plus, the improved inner molding resists cracking and reduces cable damage.

- Lightning connector provides 12W so your charger can charge your iOS devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

RUSBCLTMM1MW is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Lightning mobile devices

Features

- **DURABLE:** 3.3 ft. Heavy duty lightning cable with aramid fiber for high tensile strength increasing reliability & life of cable; Tested to withstand 10000+ bend cycles at 180 & 5000+ insertions
- **FLEXIBLE CABLE:** TPE jacket absorbs stress of frequent bends without damaging the core of the cable. Durable wire & connector protects this charge & sync cable from wear & tear of frequent in-car use
- **APPLE MFI CERTIFIED:** USB-C to lightning adapter cable for guaranteed fast & reliable charge/sync from USB-C charger port for lightning devices including iPhones Pro/Max/Mini/XR up to iPhone 14, iPad Air, iPad, iPad Mini
- **RAPIDLY CHARGE LIGHTNING DEVICES:** Rugged/strong cord supports fast charging using Power Delivery chargers from Apple 18W up to 96W USB-C adapters; Ideal for Charging Stations; Charges devices incl AirPods, Magic Keyboard/Trackpad/Mouse & Siri Remote
- **CABLE SPECS:** Length: 1 m (3.3 ft.) Color: White Connectors: Lightning & USB-C Performance: USB 2.0 480Mbps Reinforcement: Aramid Fiber Jacket Type: TPE Shield: Al-Mylar Backed by StarTech.com for 2 years

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - Apple Lightning Connector (8-pin)
	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Physical Characteristics

Color	White
Connector Style	Straight
Wire Gauge	22/32 AWG
Cable Length	3.3 ft [1 m]
Product Length	39.4 in [1000.0 mm]
Product Width	0.5 in [1.2 cm]
Product Height	0.2 in [0.6 cm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Quantity	1
Package Length	6.7 in [170.0 mm]
Package Width	3.0 in [7.6 cm]
Package Height	0.8 in [2.1 cm]
Shipping (Package) Weight	1.6 oz [46.0 g]

What's in the Box

Included in Package	1 - 1 m Lightning Cable
---------------------	-------------------------

**Product appearance and specifications are subject to change without notice.*