

USB-C Cable with Power Delivery (5A) - M/M - 1 m (3 ft.) - USB 3.1 (10Gbps) - USB-IF Certified

Product ID: USB31C5C1M



This USB-C cable with power delivery lets you power your USB Type-C devices from your USB-C laptop or charge your USB-C laptop from a USB-C wall charger. The USB 3.2 Gen 2 cable is also capable of high-speed data transfers up to 10Gbps. It's the all-in-one cable for both power and data.

With up to 5A (100W) of power output, you can use this USB Type-C cable to power your external drive from your USB-C laptop.

The cable also lets you power and charge a USB-C laptop, such as your Apple MacBook or Chromebook Pixel from a USB-C wall charger, car charger or power bank. Or, you can power your laptop from a USB-C docking station.

The 5A of power delivery lets you charge your mobile devices faster than with a regular USB-C 3.0 cable. The cable is perfect for people on the move - decrease your charge times and make sure your mobile devices are ready, whenever you need them, while you're on the road.

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 3.2 Gen 2 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable and high-quality cable for all of your USB-C devices.

The USB31C5C1M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your external USB-C drive from your USB-C laptop
- Power your USB-C laptop from a USB Type-C wall charger, car charger or power bank
- Charge your USB Type-C laptop from your docking station
- Fast charge your USB-C mobile devices from your USB-C laptop or wall charger
- Sync your USB-C mobile devices with your USB-C computer

Features

- USB-IF Certified
- Provides up to 5 amps of power output for fast-charging your mobile devices, or powering your USB-C peripheral devices or laptop
- Supports data transfer rates up to 10Gbps (USB 3.2 Gen 2)
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s
---------------	---------------------------

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)

Power

Power Delivery	100W
----------------	------

Physical

Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	26/32 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.2 in [0.6 cm]
Product Height	0.2 in [0.4 cm]
Weight of Product	1.9 oz [55.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	2.1 oz [59.0 g]

What's in the Box

Included in Package	1 - USB-C cable
---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***