# **D-Sub Connector**With Backshell Kit, 15 Ways



RoHS Compliant



### **Specification**

#### **Backshell Material**

Backshell Material : Die Cast Zinc Alloy

Plating : Nickel

Jackscrews : Steel, Zinc Plated
M3 Hoodscrews : Steel, Zinc Plated
Compression Insert : ABS, UL Recognized
Compression Spring : Steel, Nickel Plated
Operating Temperature : -40°C to +120°C

#### **Connector Material**

Shell : Steel Material, Tin Plated Finished

Insulator : PBT Thermoplastic, 30% Glass Filled, UL 94V-0 Rated, Black Colour

Contact Material : Brass
Contact Finish : GF Plated

#### **Electrical Characteristics**

Contact Current Rating : 5A

Contact Resistance :  $30m\Omega$  max Dielectric Withstanding Voltage : 1000V AC min Insulation Resistance :  $5000M\Omega$  min Temperature Rating :  $-55^{\circ}$ C to  $+105^{\circ}$ C

#### **Backshell Kit Includes**

Backshell Halves : 02 pcs
4-40 Thumbscrews : 02 pcs
Housing Screws : 02 pcs
Set Of Compression Inserts - Various Sizes : 01 pc

Diameters 4mm (0.157"), 5mm (0.167"),

7mm (0.276"), 9mm (0.354")

Compression Spring : 01 pc

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




## **D-Sub Connector**With Backshell Kit, 15 Ways


### multicomp PRO

#### Diagram












Dimensions							
Size	A ±0.5 (±0.02)	B ±0.5 (±0.02)	C ±0.5 (±0.02)	D ±0.25 (±0.01)			
15	39.5 (1.555)	41.5 (1.634)	15 (0.591)	33.32 (1.312)			







Part Number	A±0.25	B±0.13	C±0.38	D±0.25
MP013642	25.25	33.32	39.14	27.51

#### **Part Number Table**

Description	Part Number
D-Sub Connector with Backshell Kit, 15 Ways, Plug	MP013642

Dimensions: Millimetres (Inches)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



21/02/24 V1.0