D-Sub Connector With Backshell Kit, 25 Ways

multicomp PRO



RoHS Compliant

Specification

Backshell Material Backshell Plating Jackscrews M3 Hoodscrews Compression Insert Compression Spring Operating Temperature Rated voltage Rates current Contact resistance Insulation resistance Withstand voltage Temperature range

: Die Cast Zinc Alloy : Nickel : Steel, Zinc Plated : Steel, Zinc Plated : ABS, UL Recognized : Steel, Nickel Plated : -40°C to +120°C : 250V : 5A : 20MΩ max : 1000MΩ min.at 500V DC : 500V Per mintute :-55°C to 105°C


: PBT+30% GF (UL94V-0), Black

Material

Plastic Terminal

Diagram






: Brass, tin-gold plated

		Q	- A				
Dimensions							
Size	A ±0.5 (±0.02)	B ±0.5 (±0.02)	C ±0.5 (±0.02)	D ±0.25 (±0.01)			
25	53.4 (2.102)	48.6 (1.913)	15 (0.591)	47.04 (1.852)			

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

Backshell Halves	: 02 pcs
4-40 Thumbscrews	: 02 pcs
Housing Screws	: 02 pcs
Set Of Compression Inserts - Various Sizes	: 01 pc
Diameters 4mm (0.157"), 5mm (0.167"),	
7mm (0.276"), 9mm (0.354")	
Compression Spring	: 01 p2c





Dimensions : Millimetres (Inches)




D-Sub Connector With Backshell Kit, 25 Ways

multicomp PRO







Part Number	Α	В	С	D
MP013644	53.3	47.04	38.96	41.3

Part Number Table

	Description	Part Number
Dimensions : Millimetres (Inches)	D-Sub Connector with Backshell Kit, 25 Ways, Plug	MP013644

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

