

7-Port USB Charging Station with 5x 1A Ports and 2x 2A Ports

Product ID: ST7C51224EU



Charge up to seven mobile devices simultaneously. This 7-port USB charging station lets you set up a multiport charge point for tablets, phones and other mobile devices.

This standalone USB charging strip offers five 1A and two 2A USB charging ports, so you can charge several mobile devices at the same time, without having to connect to multiple wall outlets or power bars.

The 7-port charging station supports Smart Charging capabilities, including USB Battery Charging Specification 1.2 and Apple and Samsung protocols, which ensures compatibility with a broad range of mobile devices, like the Apple iPhone and iPad, the Samsung Galaxy Tab, Android devices and more.

Create a dedicated USB charging station at your desk, so you can charge your mobile devices while you work. The charging station is also a great addition to your boardroom or lobby, providing a convenient way for mobile users to keep their devices powered.

With its integrated power button, you can turn all of the ports off while the charger isn't in use.

This compact charging strip takes up minimal space and features a rugged metal housing that can withstand the wear and tear of daily use. With the included wall-mount bracket, you can attach the charging strip to a surface such as a desktop or wall, for easy access to charge ports.

ST7C51224EU is backed by a 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Charge multiple devices simultaneously
- Ideal for boardrooms, lobbies, IT helpdesks and test benches
- Install in locations where the charging strip can be securely mounted

Features

- Charge multiple devices simultaneously with five 1A ports and two 2A ports
- Free up wall outlets using a consolidated charging station
- Mount the charging strip to a desk or wall with the included mounting bracket
- Save space on your desk, work bench or conference table with the station's compact design
- Supports Smart Charging capabilities

Hardware

Warranty	2 Years
Ports	7
Industry Standards	USB Battery Charging Specification Rev. 1.2

Connector(s)

Connector Type(s)	7 - USB 2.0 Type-A (4 pin, 480Mbps)
-------------------	-------------------------------------

Indicators

LED Indicators	1 - Power
----------------	-----------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.5 A
Output Voltage	12V DC
Output Current	5 A
Center Tip Polarity	Positive
Plug Type	M

Power Consumption (In Watts) 60

Environmental

Operating Temperature 5C to 35C (41F to 95F)
Storage Temperature -20C to 50C (-4F to 122F)
Humidity 20~80% RH

Physical Characteristics

Color Black
Material Aluminum
Product Length 4.3 in [11.0 cm]
Product Width 1.8 in [4.5 cm]
Product Height 0.9 in [2.4 cm]
Weight of Product 4.2 oz [118.0 g]

Packaging Information

Package Quantity 1
Package Length 3.9 in [98.0 mm]
Package Width 9.3 in [23.5 cm]
Package Height 3.7 in [95.0 mm]
Shipping (Package) Weight 27.1 oz [767.0 g]

What's in the Box

Included in Package

- 1 - USB Charging Station
- 1 - Wallmount Bracket
- 4 - Rubber Feet
- 1 - User Manual
- 1 - Power Adapter

4 - Mounting Screws

****Product appearance and specifications are subject to change without notice.***

