

Universal Laptop Lock 6.6ft (2m), Security Cable For Notebook Compatible With Noble Wedge®/Nano/K-Slot, Keyless Combination Locking Cable, Anti-Theft Cut-Resistant Steel Cable

Product ID: UNIVC4D-LAPTOP-LOCK



The Universal Laptop Lock is a versatile solution compatible with Noble Wedge, K-Slot (T-Bar), or Nano, providing flexibility and convenience. With its on-the-fly lock tip change feature, you can quickly adapt the lock to different slot types. The cut-resistant steel security cable measures 6.5ft (2m) in length and 0.17in (4.4mm) thick, providing reach and durability. With the 3-in-1 Laptop Lock, protect your valuable devices wherever you go.

The keyless cable lock allows you to set a personalized combination code, offering up to 10,000 combinations for increased security. The lock can withstand a pull force of 202 lb (91.6 kg) for K-slot, 164.4 lb (74.6 kg) for Nano, and 110.2 lb (50 kg) for Noble Wedge, ensuring your computer or other devices remains safe from theft.

Note: The pull force values mentioned may vary if the security slots do not comply with the design standards specified by their respective manufacturers.

The versatile security lock is not limited to laptops or notebooks only. Use this lock to secure other devices such as docking stations, monitors, printers, SFF computers, projectors, oscilloscopes, or other office and lab equipment, expanding its utility. The lock is future-proof as it works with previous and newer computers from various brands, including HP, Dell, Microsoft, and more. Different thickness spacers are provided to ensure a better fit for your device.

The diameter of the lock head is 0.4in (14mm) and features a ball joint design that allows for 360 rotation and 90 pivot of the lock head. This flexibility reduces coiling and minimizes strain on the notebook slot, enhancing durability and usability.

Certifications, Reports and Compatibility



Applications

Features

- **3-IN-1 UNIVERSAL LAPTOP LOCK:** Compatible with Noble Wedge, K-Slot (T-Bar), and Nano lock slots using an adjustable lock tip; 6.5 ft (2 m) and 0.17 in (4.4 mm) thick cut-resistant carbon steel cable; Lock can withstand a pull force of up to 202lb (91.6 kg)
- **FOUR-DIGIT COMBINATION LOCK:** Keyless cable lock for laptop with user resettable combination code allowing for up to 10,000 different combinations; Includes hook-and-loop strap for storage
- **COMPATIBILITY:** Locking cable for laptop works with HP, Dell, Microsoft, and others; Notebook anti-theft lock is not brand-specific for future-proof compatibility with industry-standard security slots; Secure other office and lab equipment
- **CLEVER DESIGN:** Ball joint enables 360 rotation, and the elbow joint's 90 pivot help reduce coiling and minimize strain on the slot; Protective spacers are included to prevent damage to the laptop and improve the fit
- **FLEXIBLE INSTALLATION:** Loop the cable through a grommet hole or around a desk leg; Ideal for tradeshow and product exhibits; Accessorize with anchor locks LTANCHOR, KSLTAD, and LTANCHORL (sold separately) to safeguard equipment that lacks a security slot

Hardware

Warranty	2 Years
Compatible Lock Slot	Noble Wedge Slot Kensington Standard Slot (K-Slot) Kensington Nano Slot

Performance

Anti-theft	Yes
------------	-----

Environmental

Operating Temperature	< 28C (82.4F)
Storage Temperature	23C 2 to 55C 15 (73.4F 35.6 to 131F 59)
Humidity	70% RH

Physical Characteristics

Color	Silver & Black
Construction Material	Steel and Plastic

Product Length	6.6 ft [2.0 m]
Product Width	1.8 in [4.6 cm]
Product Height	0.6 in [1.4 cm]
Weight of Product	3.5 oz [100.0 g]

Packaging Information

Package Quantity	1
Package Length	6.3 in [16.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.9 in [2.2 cm]
Shipping (Package) Weight	5.3 oz [151.0 g]

What's in the Box

Included in Package	1 - Laptop Security Lock
	1 - Hook-and-loop Strap
	3 - Bumper Spacers
	1 - Quick-Start Guide

**Product appearance and specifications are subject to change without notice.*