



AMPLIMITE D-SUBMINIATURE CABLE ASSEMBLIES

AMPLIMITE D-subminiature cable assemblies are part of the complete line of AMPLIMITE D-subminiature connectors which has been widely used by the electronics industry for their rugged design and ease of application.

The cable assembly product line adds a selection of off-the-shelf, preassembled cable configurations that require no assembly. AMPLIMITE cable assemblies provide customers with a one-stop-shop option for wire harnesses for D-sub connectors. Customers can choose from several pre-selected options that fit their needs and applications.

All AMPLIMITE D-subminiature cable assemblies feature AMPLIMITE D-subminiature connectors with front metal-shells for EMI/RFI shielding, with housings made of UL 94 V-0 approved material, and gold plating on the contacts.

PRODUCT FACTS

- Pre-assembled, off the shelf cable assemblies
- Wide choice of configurations available
- Contact Resistance: 2 Ohms max
- Insulation Resistance: 1M Ohms min
- Tested to 300 VDC/0.15

APPLICATIONS

- Semiconductor fabrication
- Test and measurement equipment
- Medical equipment
- Datacenters
- Printers

LEARN MORE

- [Landing Page](#)

AMPLIMITE D-SUBMINIATURE CABLE ASSEMBLIES

PART NUMBERS

Part Number	Description
2478170-1	9 to 9 Male to Male 6 feet 28 AWG Cable Assembly
2478170-2	9 to 9 Male to Male 10 feet 28 AWG Cable Assembly
2478170-3	9 to 9 Female to Female 6 feet 28 AWG Cable Assembly
2478170-4	9 to 9 Female to Female 10 feet 28 AWG Cable Assembly
2478170-5	9 to 9 Male to Female 5 Feet 26 AWG Cable Assembly
2478170-6	9 to 9 Male to Female 10 feet 26 AWG Cable Assembly
2478170-7	9 to 9 Male to Female 6 feet 28 AWG Cable Assembly
2478170-8	9 to 9 Male to Female 10 feet 28 AWG Cable Assembly
1-2478170-1	15 to 15 Male to Male 2.5 feet 26 AWG Cable Assembly
1-2478170-2	15 to 15 Male to Female 2.5 feet 26 AWG Cable Assembly
1-2478170-3	15 to 15 Male to Female 5 Feet 26 AWG Cable Assembly

te.com

TE Connectivity, TE, TE connectivity (logo), and AMPLIMITE are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty, or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

©2024 TE Connectivity. All Rights Reserved.

02-24